



Recommended PCB Layout (Tolerance ±0.05)
(Copper-sided View)

PIN	Ø2.0	Ø2.35	Ø2.5



DC MATE PLUG

					TOLERANCE UNLESS SPECIFIED									
					UP TO 5mm: ±0.1	ANGULAR	1							
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD		
6	SHUNT TERMINAL	2	BRASS	1	Sn-PLATED			UNIT : MM	ROHS COMPLIANT	DWN				
5	TIP SPRING	1	SUS	1	Sn-PLATED			SCALE: 1:1	CHK'D					
4	CENTER PIN CONTACT	3	BRASS	1	Sn-PLATED	TITLE: DC JACK				APPD				
3	CENTER PIN		BRASS	1	Sn-PLATED	MODEL: DC-014 2.0								
2	COVER		PCB	1										
1	HOUSING		PBT	1										
NO.	PART NAME		MATERIAL	QTY	FINISHING									



HAOYU(HONGKONG)LIMITED
皓宇(香港)有限公司

PRO.AGL: REV :A0