









H	L
4.3	2.95
4.5	3.45
5.0	3.95
5.5	4.45
6.0	4.95
6.5	5.45
7.0	5.95
7.5	6.45
8.0	6.95
8.5	7.45
9.0	7.95
9.5	8.45
10.0	8.95

C:操作力160gf

Waterproof grade: IP67

TRAVEL:0.3±0.1mm



PCB. 焊接图

					TOLERANCE UNLESS SPECIFIED									
7	FRAME	BRASS	1	Sn-Plated	UP TO 5mm: ±0.1 ABOVE 5mm: ±0.2	ANGULAR ±1°	1							
6	TERMINAL	BRASS	2	Ag-Plated			NO	DATE	REVISIONS			BY	APPD	
5	CASE	PPA	1	BLACK	TITLE: TACT SWITCH				UNIT : MM	ROHS COMPLIANT	DWN			
4	REED	SYS301	1	Ag-Plated	MODEL: TC-00100FSA-065C				SCALE: 1:1		CHK' D			
3	WATERPROOF PAD	RUBBER	1	BLACK	 HAOYU (HONGKONG) LIMITED 皓 宇 (香 港) 有 限 公 司							APPD		
2	COVER	PPA	1	BLACK										
1	BUTTON	PPA	1	BLACK										
NO.	PART NAME	MATERIAL	QTY	FINISHING								PRO. AGL:	 	REV :A0