



RoHS


Date	Rev.	Sym.	Revisions	Signed



Real Object

PIN DESCRIPTION

PIN NO.	Pin NAME	PIN NO.	Pin NAME
1	FSIN	17	MDP1
2	DVDD	18	DOGND
3	AF_PD	19	DOGND
4	IDUT	20	VSYNC
5	AVDD	21	HREF
6	AGND	22	SID
7	SIOC	23	ILPWM
8	SIOD	24	DOGND
9	AF_VDD	25	DOVDD
10	AF_GND	26	DOGND
11	EXCLK	27	DOGND
12	MDN0	28	NC
13	MDP0	29	XSHUTDN
14	MCN	30	PWDNB
15	MCP	31	FREX
16	MDN1	32	STROBE



NOTE

- 1.Sensor: OV5693 (thickness : 200um)
- 2.IR+AR glass thickness:210um(T50%=650+/-10nm)
- 3.PCB thickness:300um
- 4.DRIVER IC:VM149C
- 5.passive: C0201 9pcs
- 6.SHICDH:TDK:TVF-603ABN / A8532M60-SE40S / ZET:ZET-8532 / MTS:M60853403
- 7.Ⓜ is Critical dimension.



東莞旺福電子有限公司

3rd ANGLE 					TITLE : PLCC,OV5693-TWD_V.01_20131217					
UNLESS OTHERWISE SPECIFIED GENERAL TOLERANCE:					MODEL :plcc		DWG NO :1/1			
DIM. LEVEL	TOLERANCE TYPE				PART NO. :		DRAWN : 勞景益			
	A	B	C	D	MATERIAL :		CHECKED : 林耕平			
	<3	±0.03	±0.03	±0.1	FINISHED :		APPROVED : 陳榮榮			
	>3~50	±0.05	±0.05	±0.1	UNIT: mm		SIZE: A4		SCALE : 1:1	REV .01
	>50~100	±0.05	±0.08	±0.15						
>100	±0.08%	±0.1%	±0.2	±0.3%						
ANGULAR	±0.5°	±0.5°	±0.8°	±1°						