




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A				

NOTES:
CURRENT RATING:2A AC/DC.
VOLTAGE RATING:125V AC/DC
TEMPERATURE RANGE:−40°C~+105°C.
CONTACT RESISTANCE:20MΩ Max.
INSULAION RESSTANCE:1000MΩ Min.
WITHSTANDING VOLTAGE: 800V AC/MINUTE.
MATERIAL:PA66+GF15%.UL94V−0.



PART NO.	DIMENSION	
	A	B
A2004WR−02P	2.00	6.00
A2004WR−03P	4.00	8.00
A2004WR−04P	6.00	10.00
A2004WR−05P	8.00	12.00
A2004WR−06P	10.00	14.00
A2004WR−07P	12.00	16.00
A2004WR−08P	14.00	18.00
A2004WR−09P	16.00	20.00
A2004WR−10P	18.00	22.00
A2004WR−11P	20.00	24.00
A2004WR−12P	22.00	26.00
A2004WR−13P	24.00	28.00
A2004WR−14P	26.00	30.00
A2004WR−15P	28.00	32.00

Recommended P.C.B Layout(Top Side)



CNJM

Joint More Precision electronics Co.,Ltd.

DRAW NO.

DESIGN:

CHECK:

REVIEW:

DATE

2017.06.03

杨 烨

P/N NO:

A2004WR−NP

REV. A/1

SCALE 1:1

DRAW NAME:

2.0mm pitch wifer

UNIT: mm

SHEET: 1 of 1