






RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.


REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM



PCB WELDING DRAWING



Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	1011Ω min.
Contact resistance	100mΩ max.initial.
Dielectric Strength	250 V AC(1mm)
Travel	0.35±0.15mm
Storage Temperature	- 30° C to 85° C

5	STEM	PPA	1	White/Black
4	COVER	Stainless Steel	1	Clean
3	DOME	Stainless Steel	1	Plated Ag
2	HOUSING	LCP	1	White
1	PIN	Brass	1	Plated Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR

Mechanical

PN	Operatin g Force (gf)	Height mm
YTS1T0161AWJ00	160±50	2.5
YTS1T0162AWJ00	250±50	2.5
YTS1T0163ARJ00	400±50	2.5

X. ±0.50	X. ° ± 2°	UNITS mm	 深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO.,LTD			
.X ±0.30	.X° ± 1°					
.XX ±0.10	.XX° ± 0.5°					
.XXX ± 0.05						
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD		FINISH 	PART NO. YTS1T016*J	TITLE: TACTILE SWITCH		
		Q' TY 	APPD: ROGER	DWG NO. : YTS1T016*J		
			CHKD: ROC			
			DR: BILLY WANG 2020/08/21	 	SCALE 1/1	SHEET 1/1

Packaging:
Reel of 3,000
pieces.