





RoHS&REACH

ECN NO.	DESCRIPTION	DATE
A-0		2020.11.14
A-1	更新细节	2021.11.27



PCB LAYOUT
(Top View)

材料Material:

- 外壳材质: PBT, PA66, PA46 (UL 94V-0)
Housing Material: PBT, PA66, PA46 (UL 94V-0)
- 触点材料: 圆针直径0.46mm磷青铜; 镀镍后镀金
Contact Material: Round Pins-0.46mm Diameter
Phosphor Bronze;
Gold Plating Over Nickel

电气Electrical

- 额定电压: 交流125伏
Voltage Rating : 125 VAC Rms
- 额定电流: 1.5安培
Current Rating: 1.5 AMP
- 接触电阻: 最大30毫欧
Contact Resistance: 30 Milliohms MaX
- 绝缘电阻: 直流500V下, 绝缘最小500兆欧
Insulation Resistance: 500 megohms min @500V DC
- 绝缘耐压: 交流60Hz 1000V下, 1分钟
Dielectric Withstanding
Resistance: 1000V AC Rms 60Hz. 1Min
- 耐久: 插拔750次以上
Durability: 750 Cycles Min
- 工作温度: -40℃~+85℃
Operation Temperature: -40℃~+85℃

5501 - X X X X X X X X X

Positions	Contacts	Shield	High	Panel	Gap	Plastic	Color	Gold Plating
4	2 or 4	0-w/O Shield 1-w/ Shield	1-H=13 2-H=15	0-w/O Panel 1-w/ Panel	0-w/O Gap 1-w/ Gap	1-PBT 2-PA66 3-PA46	1-Black 2-Gray 3-Other	1-G/Fu" 2-1u" 3-3u" 4-6u" 5-15u" 6-30u" 7-50u"

未注公差	设计	X.C.S	比例	1:1
尺寸标注	公差	审核	单位	mm
.X	±0.25 ±2.0°	批准	图幅	A4
.X	±0.20 ±1.5°	角法	版本	A-1
.XX	±0.15 ±1.0°		图数	第1页 共1页
.XXX	±0.10 ±0.5°			

恒连电子科技有限公司
EVERCOM ELECTRONIC TECHNOLOGY CO., LTD
<http://www.chinarj45.com>

产品型号 5501 13mm 4P4C 无边
产品编号 5501-440101XXX
图纸编号 HL2155A44L1