


A



DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
	0 PLC	± 0.2	
	1 PLC	± 0.2	
	2 PLC	± 0.2	
	3 PLC	± 0.2	
	4 PLC	± 0.2	
	4 PLC	± 0.2	
ANGLES		± _	
MATERIAL		FINISH	



70 WITH FLANGE TYPE 1-1747981-9

THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION SEP. 2005.
ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
J		SEE SHEET 1		-	-	-	





70	WITH FLANGE TYPE	9-1747981-1	OB
70	WITH FLANGE TYPE	8-1747981-1	OB
70	WITH FLANGE TYPE	3-1747981-1	B
70	WITH FLANGE TYPE	2-1747981-1	
70	WITH FLANGE TYPE	1-1747981-8	
70	WITH FLANGE TYPE	1-1747981-4	
70	WITH FLANGE TYPE	1-1747981-3	
70	WITH FLANGE TYPE	1-1747981-2	
70	WITH FLANGE TYPE	1-1747981-1	
QTY	CONNECTOR TYPE	PART NUMBER	

NOTICE: THIS COMMUNICATION INCLUDES TE CONNECTIVITY CONFIDENTIAL OR PROPRIETARY INFORMATION THAT MAY ALSO BE LEGALLY PRIVILEGED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity	
CHK		APVD		NAME	
DIMENSIONS: mm		PRODUCT SPEC		HDMI 19 POS	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		RECEPTACLE ASSY SMT TYPE	
0 PLC ± 0.2		108-78180-1		-LEAD FREE-	
1 PLC ± 0.2		SIZE		CAGE CODE	
2 PLC ± 0.2		A3		00779	
3 PLC ± 0.2		DRAWING NO		C=1747981	
4 PLC ± 0.2		WEIGHT		RESTRICTED TO	
ANGLES ±		CUSTOMER DRAWING		SCALE NTS	
MATERIAL		SHEET 4 of 9		REV	

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
J		SEE SHEET 1		-	-	-	



NOTICE: THIS COMMUNICATION INCLUDES TE CONNECTIVITY CONFIDENTIAL OR PROPRIETARY INFORMATION THAT MAY ALSO BE LEGALLY PRIVILEGED.

THIS DRAWING IS A CONTROLLED DOCUMENT.


DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
0 PLC	± 0.2		
1 PLC	± 0.2		
2 PLC	± 0.2	± 0.3	
3 PLC	± 0.2		
4 PLC	± 0.2		
ANGLES	± -		
MATERIAL		FINISH	

40		WITH FLANGE TYPE		1-1747981-6	
QTY		CONNECTOR TYPE		PART NUMBER	
DWN		TE Connectivity			
CHK					
APVD					
PRODUCT SPEC					
108-78180-1		HDMI 19 POS RECEPTACLE ASSY SMT TYPE -LEAD FREE-			
APPLICATION SPEC					
WEIGHT					
		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		A3	00779	C=1747981	-
CUSTOMER DRAWING				SCALE	NTS
				SHEET	5 of 9
				REV	

TE TE Connectivity


HDMI 19 POS
RECEPTACLE ASSY SMT TYPE
-LEAD FREE-

LOC	DIST	REVISIONS			DATE	DWN	APVD
J		P	LTR	DESCRIPTION			
		-		SEE SHEET 1	-	-	-




CONNECTOR WITHOUT FLANGE TYPE

NOTICE: THIS COMMUNICATION INCLUDES TE CONNECTIVITY CONFIDENTIAL OR PROPRIETARY INFORMATION THAT MAY ALSO BE LEGALLY PRIVILEGED.





P.C.B. LAYOUT
 SHOWN AS CONNECTOR MOUNTING SIDE
 TOLERANCE: NON-CUMULATIVE
 (REFERENCE)




PANEL CUT OUT DIMENSION
 (REFERENCE)

Thickness: 0.08mm color: Brown	POLYIMIDE	1	POLYIMIDE TAPE	④
	COPPER ALLOY	19	CONTACT	③
	COPPER ALLOY	1	SHELL	②
	THERMOPLASTIC UL94V-0, BLACK COLOR	1	HOUSING	①
FINISH	MATERIAL	QTY	DISCRIPTION	ITEM


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity	
CHK		APVD		NAME	
PRODUCT SPEC		108-78180-1		HDMI 19 POS RECEPTACLE ASSY SMT TYPE -LEAD FREE-	
APPLICATION SPEC		WEIGHT		RESTRICTED TO	
CUSTOMER DRAWING		SCALE 4:1		SHEET 6 OF 9	
MATERIAL		FINISH		REV	




NOTICE: THIS COMMUNICATION INCLUDES TE CONNECTIVITY CONFIDENTIAL
OR PROPRIETARY INFORMATION THAT MAY ALSO BE LEGALLY PRIVILEGED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN		 TE Connectivity	
DIMENSIONS: mm		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		NAME	
		PRODUCT SPEC		HDMI 19 POS	
0 PLC ± 0.2 1 PLC ± 0.2 2 PLC ± 0.2 3 PLC ± 0.2 4 PLC ± 0.2 ANGLES ± 0.2		108-78180-1		RECEPTACLE ASSY SMT TYPE	
MATERIAL		APPLICATION SPEC		-LEAD FREE-	
FINISH		WEIGHT		SIZE	RESTRICTED TO
				A3 00779	
				C-1747981	
		CUSTOMER DRAWING		SCALE	REV
				NTS	7 of 9

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—		—	SEE SHEET 1	—	—	—



P.C.B LAYOUT
SHOWN AS CONNECTOR MOUNTING SIDE
TOLERANCE: NON-CUMULATIVE
(REFERENCE)



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP , 2005.

© COPYRIGHT 2005 By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

-


SEE SHEET 1

-


-

-

NOTICE: THIS COMMUNICATION INCLUDES TE CONNECTIVITY CONFIDENTIAL
OR PROPRIETARY INFORMATION THAT MAY ALSO BE LEGALLY PRIVILEGED.



CONNECTOR
WITHOUT FLANGE TYPE



CONNECTOR
WITH FLANGE TYPE

MATING CONDITION (REFERENCE)
(SCALE 2:1)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± 0.2
1 PLC ± 0.2
2 PLC ± 0.2
3 PLC ± 0.2
4 PLC ± 0.2
ANGLES $\pm -$

MATERIAL

FINISH

DWN

CHK

APVD

PRODUCT SPEC

108-78180-1

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

HDMI 19 POS
RECEPTACLE ASSY SMT TYPE
-LEAD FREE-

SIZE

CAGE CODE

DRAWING NO

A3 00779 C-1747981

RESTRICTED TO

SCALE 2:1

SHEET 9 OF 9

REV