









版本	变更内容	工程确认	日期




- TYPE C USB技术要求:
1. 电气性能
 - 1.1. 额定电流: 3A/5A.
 - 1.2. 额定电压: 5V.
 - 1.2. 耐电压: 500 V(AC) for 1 min.
 - 1.3. 接触阻抗: 40mΩ Max.
 - 可靠性: 可靠性和环境测试后阻抗变化不得超过10mΩ.
 - 1.4. 绝缘阻抗: 100 MΩMin.
 2. 机械性能
 - 2.1. 插入力: 5-20N. 拔出力: 6-20N.
 - 2.2. 寿命测试: 5000/10000cycles Max.
 - 2.3. 推力: 50N min.
 - 2.4. 剥离强度: 150N min.
 - 2.5. 扭曲强度: 0.75Nm
 3. 材料要求
 - 4.1. 胶芯材料: LCP/PA9T
 - 4.2. 外壳材料: SPCC/C2680/SUS304
 - 4.3. 端子材料: C2680/C5191/C7025
 4. 盐雾要求: 24H/48H
 5. 工作温度: -20° C~85° C



RECOMMENDED P.C.B. LAYOUT



 深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO., LTD		页码 (SHEET)	1/1	单位(UNIT): MM
品名 (ITEM NO)		版本 (REV)	A1	比例(SCALE)
料号 (PART NO)		日期 (DATE)	2021. 10. 12	
图号 (DWG NO)		设计 (DESIGN)	LUO	未注公差 TOLERANCE UNSPECIFIED
		审核 (CHECKED)	ROGER LI	X. X ±0.20 X. XX ±0.15 X. XXX ±0.10
		核准 (APPROVED)	ROC ZHAO	X° ±5° X. X° ±2°
These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd.The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd.Prior written consent to copy or use in any way				