








CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM



PCB.WELDING DRAWING

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	1011Ω min.
Contact resistance	100mΩ max.initial.
Dielectric Strength	250 V AC(1mn)
Travel	0.15±0.1mm
Storage Temperature	- 30° C to 80° C

C	DOME	Stainless Steel	1	Plated Ag
B	HOUSING	LCP	1	Black
A	Cards	Phosphor copper	1	Plated Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/CO LOR

Mechanical

P/N	Operatin g Force(grf)	Heiht mm	Button	Leads Shape (0,J,T)	Ground pin (0,1)	Pegs Option (0,1)
YTS1H002	2	250±50				
	1	180±50	A	0.55		

X. ±0.50	X.° ± 2°	UNITS mm	 深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO.,LTD				
.X ±0.30	.X° ± 1°						
.XX ±0.10	.XX° ± 0.5°	MAT'L 		PART NO. YTS1H002		TITLE: TACTILE SWITCH	
.XXX ±0.05							
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD		FINISH 	APPD: ROGER		DWG NO. : YTS1H002		
			CHKD: ROC				
		Q' TY 	DR: BILLY WANG 2020/08/21		 		
			SCALE	SHEET	REV.		
			1/1	1/1	A1		

Packaging:
a reel of 5,000 pieces