


SCHEMATIC



P.C.B.LAYOUT

* CRITICAL DIMENSION

ELECTRICAL CHARACTERISTICS


1. RATING: DC 30V 0.1A
2. CONTACT RESISTANCE: 100mΩ MAX
3. INSULATION RESISTANCE: 100MΩ MIN
4. DIELECTRIC STRENGTH: AC 250V (50~60Hz)/60S

MECHANICAL CHARACTERISTICS

1. PRACTICAL TEMPERATURE RANG: -40°C ~ +85°C
2. OPERATING FORCE: 400 ± 50gf
3. MECHANICAL LIFE: 20,000 cycles

NO.	PART NAME	Q' TY	MATERIAL	FINSH/COLOR
7	CAM STICK	1	SUS	NATURAL
6	TERMINAL	6	BRASS STRIP	Ag COATING
5	CASE	1	PA66	GRAY
4	CONTACT	2	BRONZE	Ag CLAD
3	COVER	1	PPA	BLACK
2	SPRING	1	SUS	NATURAL
1	KNOB	1	POM	WHITE

X. ± 0.50	X. ° ± 2°	UNITS mm
.X ± 0.30	.X° ± 1°	
.XX ± 0.10	.XX° ± 0.5°	MAT'L /
.XXX ± 0.05		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD		FINISH /
		Q' TY /



深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO., LTD

PART NO.
YTS85NL400CW

APPD: ROGER

CHKD: ROC

DR: BILLY WANG 2020/08/21

TITLE:
规格8.5*8.5 按钮2*3按钮

DWG NO. :
YTS85NL400CW

SCALE	SHEET	REV.
1/1	1/1	A1