





| REV. | MODIFICATION    | DATE       | DRAW    |
|------|-----------------|------------|---------|
| A    | INITIAL RELEASE | 2021.01.11 | Michael |
| B    | ECR-2021002     | 2021.03.23 | Michael |
| C    | ECR-2021008     | 2021.09.17 | Michael |

HALOGEN FREE LEAD FREE



MATING: ① INSERTING → ② ROTATING → ③ FIXED  
UNMATING: ④ UNFIXED → ⑤ ROTATING → ⑥ WITHDRAWING

MATING/UNMATING VIEW  
SCALE 2:1

- NOTES
1. MATERIAL:  
HOUSING: THERMOPLASTIC UL94V-0  
CONTACT: HIGH-PERFORMANCE COPPER ALLOY  
LATCH: STAINLESS STEEL  
PEG: STAINLESS STEEL
2. FINISH:  
CONTACT: GOLD PLATING ON CONTACT AREA (SEE NOTE 4)  
1u"~3u" GOLD PLATING ON SOLDER AREA  
NICKEL UNDER PLATING OVER ALL (SEE TABLE 1)  
PEG: 50u"~150u" MATTE TIN PLATING OVER ALL  
50u"~150u" NICKEL UNDER PLATING OVER ALL
3. MSL LEVEL:  
MSL (MOISTURE SENSITIVITY LEVEL)=1
4. PART NO.:

|                                |                                                                 |
|--------------------------------|-----------------------------------------------------------------|
| D5ASX-262XX-XX40               |                                                                 |
| Ni PLATING SPEC<br>SEE TABLE 1 | PACKING<br>P:TAPE REEL<br>HOUSING COLOR<br>1:BLACK<br>2:NATURAL |
| CONTACT AREA<br>PLATING SPEC   |                                                                 |
| 01:GOLD 1u"Min.                |                                                                 |
| 03:GOLD 3u"Min.                |                                                                 |
| 05:GOLD 5u"Min.                |                                                                 |
| 10:GOLD 10u"Min.               |                                                                 |
| 15:GOLD 15u"Min.               |                                                                 |
| 20:GOLD 20u"Min.               |                                                                 |
| 30:GOLD 30u"Min.               |                                                                 |

LINKTEK

TABLE 1

|                |                |                          |
|----------------|----------------|--------------------------|
| N              | WITH "®LTK"    | 90u"~150u"               |
| A              | WITHOUT "®LTK" | 50u"~150u"               |
| 0(NUMBER ZERO) | WITH "®LTK"    | 50u"~150u"               |
| X              | TRADEMARK      | CONTACT<br>NICKEL FINISH |

|                                         |          |                            |
|-----------------------------------------|----------|----------------------------|
| DIMENSION IN mm [Inch]                  |          | PROD. SPEC.<br>SP-D5XXL1   |
| TOLERANCE UNLESS<br>OTHERWISE SPECIFIED |          | PKG. SPEC.<br>PK-D5XXX-XXX |
| .X ± 0.35                               | X.* ± 2° | APR. Kevin<br>2021.09.17   |
| .XX ± 0.25                              | .X.* ±   | CHK. Andy<br>2021.09.17    |
| .XXX ±                                  | .XX.* ±  | DRA. Michael<br>2021.09.17 |


ARGOSY RESEARCH INC.

TITLE: DDR5 4.0H STD CONNECTOR

FILE NO. N/A DWG NO. D5ASX-262XX-XX40

PROJ. CUSTOMER DRAWING

SHEET 1/2 REV. C C



| REV. | MODIFICATION    | DATE       | DRAW    |
|------|-----------------|------------|---------|
| A    | INITIAL RELEASE | 2021.01.11 | Michael |
| B    | ECR-2021002     | 2021.03.23 | Michael |
| C    | ECR-2021008     | 2021.09.17 | Michael |


HALOGEN FREE LEAD FREE

RECOMMEND P.C.BOARD LAYOUT  
PCB THICKNESS 0.80mm MIN.  
PCB LAYOUT GENERIC TOLERANCE:±0.05  
(-Z-:PCB SURFACE)

| DIMENSION IN mm [Inch]               |        | PROD. SPEC.<br>SP-D5XXXL1  |
|--------------------------------------|--------|----------------------------|
| TOLERANCE UNLESS OTHERWISE SPECIFIED |        | PKG. SPEC.<br>PK-D5XXX-XXX |
| .X±0.35                              | X.*±2° | APR. Kevin<br>2021.09.17   |
| .XX±0.25                             | .X.*±  | CHK. Andy<br>2021.09.17    |
| .XXX±                                | .XX.*± | DRA. Michael<br>2021.09.17 |

| ARGOSY RESEARCH INC.           |                          |        |   |
|--------------------------------|--------------------------|--------|---|
| TITLE: DDR5 4.0H STD CONNECTOR |                          |        |   |
| FILE NO. N/A                   | DWG NO. D5ASX-262XX-XX40 |        |   |
| PROJ.                          | CUSTOMER DRAWING         |        |   |
| SHEET 2/2                      | SCALE 1:1                | REV. C | C |

LINKTEK



HALOGEN FREE LEAD FREE

| PART NO.          | PCS/REEL | REEL/CARTON | PCS/CARTON |
|-------------------|----------|-------------|------------|
| D5XRX-262XX-XP40X | 500      | 3           | 1.50K      |
| D5XSX-262XX-XP40X | 500      | 3           | 1.50K      |

|                    |                |                     |                    |                       |            |           |                         |             |             |
|--------------------|----------------|---------------------|--------------------|-----------------------|------------|-----------|-------------------------|-------------|-------------|
| 包裝規範(PACKING LIST) | 產品名稱<br>TITLE  | 案 號<br>FILE NO.     | 更改<br>REV          | 張數<br>SHEET           | SIZE<br>A4 |           |                         |             |             |
|                    | 圖 號<br>DWG NO. | 審 核<br>APPROVE      | 核 對<br>CHECK       | 製 圖<br>DRAW           |            | A         | INITIAL RELEASE         | 2021.06.16  | Michael     |
|                    | PK-D5XXX-001   | Kevin<br>2021.06.16 | Andy<br>2021.06.16 | Michael<br>2021.06.16 |            | 更改<br>REV | 設 變 內 容<br>MODIFICATION | 日 期<br>DATE | 修 改<br>DRAW |