






Code-x	H	Code-x	H
A	4.3	O	11.0
B	4.5	P	11.5
C	5.0	Q	12
D	5.5	R	12.5
E	6.0	S	13.0
F	6.5	T	13.5
G	7.0	U	14.0
H	7.5	V	15.0
I	8.0	W	15.5
J	8.5	X	16
K	9.0	Y	16.5
L	9.5	Z	17
M	10.0	18	18
N	10.5	19	19

SPECIFICATION
Contact Rating: 50mA,12V DC
Contact Resistance: 100mΩ max
Insulation Resistance: 100mΩ min.500V DC
Dielectric Strength: 250V AC/1minute
Travel: 0.25mm
Operating Temp: -20℃~+70℃
Storage Temp: -40℃~+85℃

CIRCUIT DIAGRAM



P.C.B MOUNTING HOLES



PACKING REEL TYPE

PAPT NO	TS-1102SD-X-X-X
Operating Force	A:100gf B:160gf C:260gf
Height	Code-x
Color	B:Black BR:Brown R:Red O:Orange Y:Yellow BL:Blue W:White

⑤	Terminal	—	4	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	Pa46	—	—
②	Cover	—	1	Bass	Plating Nickel	—
①	Keystake	—	1	Pa46	—	—
ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK

					units: mm	DSND		DATE		SCALE: N/A	MODEL TYPE:
					tolerance:	DWN		DATE		VIEW:	TACT SWITCH
					X.X ±0.2mm	CHKD		DATE		UNIT: mm/in	PART NO.:
					X.XX ±0.1mm	APPD		DATE		SIZE: A4	DWG NO.:
					X.XXX ±0.05mm						TS-1102SD-X-X-X
					UNSPECIFIED TOLERANCES						WEIGHT
											1.0g
											SHEET
											1/1
											REVISION
											A0