




RoHS 2.0

PIN NUMBER	SIGNAL NAME
PIN 1	Vbus
PIN 2	D-
PIN 3	D+
PIN 4	GND
PIN 5	StdA_SSRX-
PIN 6	StdA_SSRX+
PIN 7	GND_DRAIN
PIN 8	StdA_SSTX-
PIN 9	StdA_SSTX+
SHELL	GND



3D VIEW



目錄	設變內容	日期

NOTES:

- MATERIAL:
  - HOUSING: LCP ,COLOR IS BLUE;
  - CONTACT: BRASS, (H65 T=0.20mm);
  - SHELL: COLD ROLLED IRON (SPCC,T=0.3mm);
- FINISH:
  - TERMINAL:
    - CONTACT AREA: GOLD PLATED G/Fu";
    - SOLDER AREA: PLATED OVER TIN;
  - SHELL: NI PLATED OVER ALL ;
- ELECTRICAL:
  - VOLTAGE RATING: 30 VAC RMS;
  - CURRENT RATING: 1.5 AMP;
  - CONTACT RESISTANCE: 30MILLIOHMS MAX.;
  - WITHSTAND VOLTAGE: 500 VAC RMS  
50(60)Hz,1MIN.;
  - INSULATION RESISTANCE: 100MEGOHMS MIN  
@500V DC;
- MECHANICAL:
  - MATING FORCE: 35N MAX.;
  - UNMATING FORCE: 5~35N;
  - OPERATING LIFE: 1500 CYCLES MIN.;
- ENVIRONMENTAL:
  - STORAGE TEMPERATURE RANGE: -40°C~+85°C;
  - OPERATION TEMPERATURE RANGE: -25°C~+70°C;

产品图  
PRODUCT CHART DWG

深圳市精拓金电子有限公司

公差一览表 (TOLERANCE UNLESS OTHERWISE S)				单位	MM	制图	张如波	产品料号 PRODUCT PART NO.	903-631A202CS10100
X.	±0.40	X'	±5°	比例	1:1	审核	郭治富	产品名称 PRODUCT NO.	AF/3.0无后盖14.2短直脚有边铁壳蓝胶端子SMT
.X	±0.30	.X'	±3°						
.XX	±0.20	.XX'	±1°						
.XXX	±0.10	.XXX'	±0.5°	日期	2022/05/10	核准	黄国荣	角法 VIEW	⊕ ⊞
								版本	A0