





XKB



Specifications:
 规格:
 Voltage rating:50V AC/DC
 额定电压: 50V AC/DC
 Current rating:1A AC/DC
 额定电流: 1A AC/DC
 Withstanding voltage:250V AC/minute
 耐受电压: 250V AC/分钟
 Temperature range:-25 °C-+85°C
 温度范围: -25°C-+85°C
 Insulation resistance:≥100MΩ MIN
 绝缘电阻: ≥100MΩ
 Contact resistance:20mΩ MAX
 接触电阻: ≤20mΩ
 Applicable wire Range:AWG#28-#32
 使用线范围: AWG #28-#32

X1004 - H - 2xXX - N0
 ① ② ③ ④

- ① Series No.
- ② Category:H-HSG
- ③ Row No .-pln No. :2xXX-2*08、2*10、2*15、2*16、2*20、2*25
- ④ Material N0:PA66 UL94-0



PIN	DIM.(MM)	
	A	B
2X08	7.00	9.70
2X10	9.00	11.70
2X15	14.00	16.70
2X16	15.00	17.70
2X20	19.00	21.70
2X25	24.00	26.70

Autodesk

Autodesk

广东星坤科技股份有限公司

生效 日期

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	XKB	ANGLAR	±5°	DSND	DATE	SCALE: N/A	MODEL TYPE:		
							L ≤ 4	±0.2	DWN	DATE	VIEW:	PART NO.:		
							4 < L ≤ 16	±0.3	CHKD	DATE	UNIT: mm/in	2.54 mm Crimp Style Connectors		
							16 < L ≤ 63	±0.4	APPD	DATE	SIZE: A4	DWG NO.:		
							L > 63	±0.5				X1004H-2xXX-N0		
XKB INDUSTRIAL PRECISION CO., LIMITED												WEIGHT	SHEET	REVISION
												1.0g	1/1	A0