



■ Specifications :



- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10mΩ
- After environmental testing : ≤20mΩ



X8826 W V-2*XX- N0 XX

- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : V-Stright 180°
- ④ Row No.-Pin No.: 2*XX-Double Row
- ⑤ Material : N0-PA66 94V-0
- ⑥ Plating Category: Sn-Bright Tin Plating(70u")

Poles	Dimensions(mm)	
	A	B
02	2.50	7.50
03	5.00	10.00
04	7.50	12.50
05	10.00	15.00
06	12.50	17.50
07	15.00	20.00
08	17.50	22.50
09	20.00	25.00
10	22.50	27.50
11	25.00	30.00
12	27.50	32.50
13	30.00	35.00
14	32.50	37.50
15	35.00	40.00
16	37.50	42.50
17	40.00	45.00
18	42.50	47.50
19	45.00	50.00
20	47.50	52.50



X8826WV-2*XX-N0SN	Nyoln 66 UL 94V-0	Brass	Tin-Plated	X8826H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

ΔX		日期
ΔX		
ΔX		
MARK	DESCRIPTION	

文件工程章

						ANGLAR	±5°	DSND		DATE		SCALE: N/A	MODEL TYPE:
						L≤4	±0.2	DWN		DATE		VIEW:	X8826WV-2*XX-N0SN
						4<L≤16	±0.3	CHKD		DATE		UNIT: mm/in	PART NO.:
						16<L≤63	±0.4	APPD		DATE		SIZE: A4	2.5mm Crimp Style Connectors
						L>63	±0.5						DWG NO.:
						UNSPECIFIED TOLERANCES							X8826WV-2*XX-N0SN
													WEIGHT
													1.0g
													SHEET
													1/1
													REVISION
													A0

XKB INDUSTRIAL PRECISION CO.,LIMITED