



3

7.62xN+10.58

1Y
(Color) : 1.(Grey)
2.(Blue)
3.(Black)
4.(Green)
5.(Orange)
6.(Red)
7.(Transparent)
8.(Yellow)
9.(White)



3	Nut	Copper alloy	/		
2	Pin	Copper	Sn Plated		
	Housing	PA66	UL94V-0		
ITEM	NAME OF PART	MATERIAL	NOTES		
UL 标准/UL Standard:			B	C	D
额定电压/电压/Rated Voltage(V)/Current(A)		300/15	/	/	300/10
EC 标准/IEC Standard:					
过压类别/Overvoltage Category/污染等级/Pollution Degree		III/3	III/2	II/2	
额定电压/电压/Rated Voltage(V)/Current(A)		/	400/20	/	
额定脉冲电压/(KV)/Rate Impulse Voltage(KV)		/	4	/	
线数范围/Poles		N=02~12P			
使用温度范围/Operating temperature(°C)		-40~+105			
符合RoHS环保要求/Conform to RoHS		Yes			

MATERIAL:		SURFACE:			
MAT NO.: /		 宁波高松电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD			
STATUS: /					
APPD: Lan ChH 2020.05.21		NAME:			
CHKD: /		2EDGVM-7.62-XXP-1Y-100A(H)			
DRFT: GongYZh 2020.05.21		DRAWING NO.:	10002012	REV	TO
	SIZE: A4		mm (inch)	TYPE: CUSTOMER DRAWING	SCALE: 2:1 SHEET 1/1

REV	ECN	DESCRIPTION	DRFT	DATE		SIZE: A4		TYPE: CUSTOMER DRAWING	SCALE: 2:1	SHEET	1/1
		3	4			5			6		