
CAD FILE:


Technical Data
Material:
Contact material:Brass
Plating:Gold Flash
Insulator material:Black polyester UL94V-0
Standard:PBT+30%G.F

Electrical:
Current rating:3Amps/contact max.
Contact resistance:≤20mΩ/contact
Insulation resistance:≥1000MΩ at V=100V
Withstanding voltage:550V AC/minute


Mechanical:
Soldering temperature:+220℃,4s max


UNSPECIFIED TOLERANCE:±0.20





PCB Layout





PIN NUMBER	A(mm)	B(mm)	C(mm)
6P	15.24	5.08	12.94
8P	17.78	7.62	15.48
10P	20.32	10.16	18.02
12P	22.86	12.70	20.56
14P	25.40	15.24	23.10
16P	27.94	17.78	25.64
18P	30.48	20.32	28.18
20P	33.02	22.86	30.72
22P	35.56	25.40	33.26
24P	38.10	27.94	35.80
26P	40.64	30.48	38.34
28P	43.18	33.02	40.88
30P	45.72	35.56	43.42
32P	48.26	38.10	45.96
34P	50.80	40.64	48.50
36P	53.34	43.18	51.04
40P	58.42	48.26	56.12
44P	63.50	53.34	61.20
50P	71.12	60.96	68.82
60P	83.82	73.66	81.52
64P	88.90	78.74	86.60

DEALON 德之隆

APPROVALS		DATE
DRAWN	G.M.Chen	2015/5/4
CHECKED		
APPROVALS		

DEALON 德之隆® ELECTRONICS CO.,LTD

TITLE:	简牛2.54 nP 90度
PART NO.	DW254P-2X口-L0
UNIT: mm	SCALE: 1:1
DRAWING NO.	SHEET 1 OF 1
	PROJ:

TOLERANCES ARE			ANGLE
30~以上	±0.30		
10~30	±0.20		
5~10	±0.15	±2°	
~ 5	±0.10		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			