



Specifications:
 规格:
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Voltage rating:250V AC
 额定电压: 250V AC
 Withstanding voltage:500V AC/MIN
 耐受电压: ≥500V AC/分钟
 Temperature range:-55°C~+105°C
 温度范围: -55°C~+105°C
 Insulation resistance:1000MΩMIN
 绝缘电阻: ≥1000MΩ
 Contact resistance:30mΩMAN
 接触电阻:≤30mΩ
 Material And FINISHED:
 材料和成本:
 INSULATOR:PBT UL 94V-0
 绝缘体: PBT UL 94V-0
 SHELL: SPCC-SD Plated Ni / Au / Sn
 外壳: 铁合金 镀镍/金/锡
 CONTACT MATERIAL:COPPER ALLOY
 触点材料: 铜合金

X03 XX F T X X X
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No.Pin No:XX-09;15;25;37
- ③ Welding Board Angle :F-Female
- ④ T:Tradutional
- ⑤ Planting Categoty:1:1U' ;2:2U' ;3:3U' ;4:5U' ;5:15U' 6:30U' ;7:AuSn
- ⑥ B:Black W:White BL:Blue Y:Yellow G:Green R:Red
- ⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 6:TYPE-6

NO.OF CONTACT	A	B	C
09	30.80	24.99	16.35
15	39.20	33.30	24.75
25	53.05	47.04	38.35
37	69.40	63.50	54.75

铆合方式	TYPE-1: 铆合	TYPE-6: 直铆锁	TYPE-3: 叉锁	TYPE-2: 铆合锁螺丝
图式				

DSND		SCALE: N/A	MODEL TYPE: D-USB
DWN		VIEW:	PART NO.: X03XXFTXXX
CHKD		UNIT: mm/in	DWG NO.: X-X03XXFTXXX
APPD		SIZE: A4	WEIGHT SHEET REVISION 1/1 A0

广东星坤科技股份有限公司

DATE	DESCRIPTION	REVISIONS
DATE	DESCRIPTION	REVISIONS

文件工程章

DATE	REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

XKLB

XKB INDUSTRIAL PRECISION CO., LIMITED