




1		2		3	
STRUCTURE (构造)					
NO.	ITEM(项目)	SPECIFICATION (规格)			
1	INSULATION (胶膜)	印字:E488937 UL20624 (43μm)			
		白膜:80℃ 60V (43μm)			
2	SUPPORTING TAPE (补强板)	225μm			Blue(蓝色)
3	CONDUCTOR (导体)	Thickness(厚度)	0.035	±0.005	
		Width(宽度)	0.3	±0.03	
	CONDUCTOR (导体镀层)	PLATED(电镀)	锡Sn (1μm)	MIN	
		PLATED(电镀)			
DIMENSION (尺寸)					
No. of conductors (导体数目)		N	8		
Pitch(间距)		P	0.5	±0.05	
Span(总间距)		SP	3.5	±0.05	
Width(总宽度)		W	4.5	±0.08	
Margin(边缘宽度)		M	0.5	±0.07	
Total length(总长度)		TL	50	±2.0	
Insert Thickness (插接端厚度)		T	0.3	±0.03	
Surface Thickness (线身厚度)		ST	0.12	±0.03	
E	Strip Length (裸铜长度)	S1	3.0	±0.5	
		S2	3.0	±0.5	
	Supporting Tape Length(补强板长度)	B1	5.0	±1.0	
		B2	5.0	±1.0	

技术要求:

1、保存环境:
温度: 15~25℃ 湿度: 30~50RH%

2、保质期:
镀金: 12个月 镀锡: 6个月

3、产品符合ROHS2.0标准

Customer P/N(客户料号):			C29534		深圳市连线电子有限公司				
NO.	DESCRIPTION (描述)	DATE	Drawing:		Title: FFC CABLE				
0	NEW DRAWING(新作成)	2019. 09. 12	(绘制) 陈历祥		0. 5*8*50*A (3/3/5/5) (0. 035*0. 3)				
			Check:		Customer(客户)	A771		Rev. (版次)	A/0
			(审核)						
			Approved:		Dwg NO. (图纸编码)			Page	1/1
			(核准)					(页码)	
			Unit: mm		P/N(料号)			Weight	
								(重量)	