




8 7 6 5 4 3 2 1

NO.	ECN NO.	DESCRIPTION	REV.	DRAW	DATE
1		新版发行	A0	廖振纲	20200728
2					

1. MECHANICAL DIMENSINS:



RECOMMENED PLUG DIMENSION:




未注公差 TOLERANCE UNLESS OTHERWISE SPECIFIED				E-NETTR 东莞市祥星电子有限公司 DONGGUANG XIANGXING ELECTRONICS CO., LTD			
				Miss yang:13694998066 Mr Li:15013501940 TEL:0769-86384669 FAX:0769-81813600 Http://www.e-nettr.com xxing.guang@163.com			
比例 SCALE		角法 PROJ.	设计 DESIGN	品号 ITEM NO.			
张数 SHEET	1/3	纸张 SIZE	A4	品名 TITLE	GR01M2HXS004		
单位 UNIT	mm	版本 REV.	A0	规格 DESC.			

8 7 6 5 4 3 2 1


NO.	ECN NO.	DESCRIPTION	REV.	DRAW	DATE
1		新版发行	A0	廖振纲	20200728
2					

2. PCB LAYOUT:




PCB LAYOUT

3. LED Configuration



未注公差 TOLERANCE UNLESS OTHERWISE SPECIFIED				E-NETTR 东莞市祥星电子有限公司 DONGGUANG XIANGXING ELECTRONICS CO., LTD Miss yang:13694998066 Mr Li:15013501940 TEL:0769-86384669 FAX:0769-81813600 Http://www.e-nettr.com xxing.guang@163.com			
比例 SCALE		角法 PROJ.		设计 DESIGN		品号 ITEM NO.	
张数 SHEET	2/3	纸张 SIZE	A4	校对 CHECK		品名 TITLE	GR01M2HXS004
单位 UNIT	mm	版本 REV.	A0	核准 APPROVAL		规格 DESC.	

4. SCHEMATIC:




5. NOTES:

- ELECTRICAL:**
 CURRENT RATING: 1.5A
 VOLTAGE RATING: 125V AC
 INSULATION RESISTANCE: 500MΩ Mini
 WITHSTAND VOLTAGE: AC 1500 V RMS 50Hz OR 60Hz 1 Min
 CONTACT RESISTANCE: 20mΩ Max
- MECHANICAL:**
 INSERTION FORCE: 2 CONTACTS----350g 4 CONTACTS----500g
 6 CONTACTS----750g 8 CONTACTS----900g
 RETENTION STRENGTH: 7.7Kg BETWEEN JACK AND PLUG
 DURABILITY: 750 MATING CYCLES Mini
- HOUSING:** 1) GLASS FILLED PA66 (UL 94V-0)
 2) GLASS FILLED PA46 (UL 94V-0)
 3) GLASS FILLED PBT (UL 94V-0)
- MATERIAL:**
 SPRING WIRE: 1) 0.45*0.35mm DIA PHOSPHOR BRONZE GOLD PLATING OVER NICKEL
 2) 0.35mm THICKNESS PHOSPHOR BRONZE ALLOY SELECTIVE GOLD PLATING OVER NICKEL
 SHIELDING: 0.20mm THICKNESS COPPER ALLOY WITH TIN PLATED
 GOLD PLATING: 3u", 6u", 15u", 30u", 50u"
 WORKING TEMPERATURE: -40c-70c

ELECTRICAL SPECIFICATIONS AT 25 °C

Insertion Loss dB max	Return Loss dB min			Crosstalk(db TYP)			Common Mode Rejection (dB TYP)		High Impedance
	1-100MHz	1-30MHz	30- 60MHz	60- 80MHz	1-30MHz	30- 60MHz	60- 80MHz	1-50MHz	
-1.0	-20	-16	-12	-40	-35	-30	-30	-20	1500



NO.	ECN NO.	DESCRIPTION	REV.	DRAW	DATE
1		新版发行	A0	廖振纲	20200728
2					

未注公差 TOLERANCE UNLESS OTHERWISE SPECIFIED				E-NETTR 东莞市祥星电子有限公司 DONGGUANG XIANGXING ELECTRONICS CO., LTD Miss yang:13694998066 Mr Li:15013501940 TEL:0769-86384669 FAX:0769-81813600 Http://www.e-nettr.com xxing.guang@163.com			
比例 SCALE		角法 PROJ.	⊕	设计 DESIGN		品号 ITEM NO.	
张数 SHEET	3/3	纸张 SIZE	A4	校对 CHECK		品名 TITLE	GR01M2HXS004
单位 UNIT	mm	版本 REV.	A0	核准 APPROVAL		规格 DESC.	