








H	X
4.3	3.15
5.0	3.85
6.0	4.85
7.0	5.85
7.3	6.15
7.5	6.35
8.0	6.85
8.5	7.35
9.0	7.85
9.5	8.35
10.0	8.85
11.0	9.85
12.0	10.85
13.0	11.85
14.0	12.85
15.0	13.85
15.5	14.35
16.0	14.85
17.0	15.85

E:操作力 160 ± 50

					TOLERANCE UNLESS SPECIFIED							
					UP TO 5mm:±0.1	ANGULAR	1	2017.1.13	更新图面			
					ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS		BY APPD	
4	CONTACT FOOT	BRASS	2	Ag-PLATED	TITLE:TACT SWITCH				UNIT : MM	ROHS	DWN	
3	COAT	BRASS	1	Ni-PLATED	MODEL: TC-00100-043C				SCALE: 1:1	COMPLIANT	CHK'D	
2	BUTTON	PC	1		 HAoyu(HONGKONG)LIMITED				APPD		PRO.AGL: 	
1	HOUSING	PA66	1									
NO.	PART NAME	MATERIAL	QTY	FINISHING							REV :A1	