

Specifications:

规格:

Voltage rating:50V AC/DC

额定电压: 50V AC/DC

Current rating:0.5A AC/DC

额定电流: 0.5A AC/DC

Withstanding voltage:200V AC/minute

耐受电压: 200V AC/分钟

Temperature range:-40°C~+105°C


温度范围: -40°C~+105°C

Insulation resistance:500MΩ Max


绝缘电阻: 500MΩ Max

Contact resistance:20mΩ Max


接触电阻: 20mΩ Max



X方向浮动量/X Directio : ±0.7mm






Y方向浮动量/Y Directio : ±0.7mm





X0635 F V S - XX A S- LP V01

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- 1.Series No
- 2.Category:Female
- 3.Welding Board Angle:V-Straight 180°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:XX-20~100P
- 6.Height:A=6.3mm, Mating height 6.3±0.5
- 7.Special No:S-With positioning column
- 8.Material:LP-LCP UL94V-0
- 9.Plating:V01-Gold paltd 4u" MIN



SECT:A-A  
2:1



PCB LAYOUT

Poles	Dimensions(mm)			
	A	B	C	D
20	14.650	13.450	5.715	10.650
30	17.825	16.625	8.890	13.825
40	21.000	19.800	12.065	17.000
50	24.175	22.975	15.240	20.175
60	27.350	26.150	18.415	23.350
70	30.525	29.325	21.590	26.525
80	33.700	32.500	24.765	29.700
90	36.875	35.675	27.940	32.875
100	40.050	38.850	31.115	36.050

X0635FVS-XXAS-LPV01	LCP	Phosphor Bronze	X0635W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

DSND	SCALE: N/A	MODEL TYPE: 0.635mm BTB Connector
DWN	VIEW:	PART NO.: X0635FVS-XXAS-LPV01
CHKD	UNIT: mm/in	DWG NO.: X-X0635FVS-XXAS-LPV01
APPD	SIZE: A4	WEIGHT
		SHEET
		REVISION
		1/1
		A0

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO., LIMITED

广东星坤科技股份有限公司

DATE	DATE	DATE	DATE
DATE	DATE	DATE	DATE
DATE	DATE	DATE	DATE
DATE	DATE	DATE	DATE

文件工程章

REVISIONS	DATE	REVISIONS	DATE
REVISIONS	DATE	REVISIONS	DATE
REVISIONS	DATE	REVISIONS	DATE
REVISIONS	DATE	REVISIONS	DATE

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn