

主要技术规格:

1. 额 定 值: 50mA DC12V
2. 接触电阻: $\leq 50\text{m}\Omega$
3. E(操 作 力): $250 \pm 40\text{gf}$
4. 行 程: $0.3 \pm 0.1\text{mm}$
5. 绝缘电阻: $\geq 100\text{M}\Omega$
6. 抗电强度: 250V 50HZ 1Min.
7. 寿 命: 100,000 Cycles
8. 防水等级: IP67
9. 防银迁移: 60V, 85°C, 90%RH/60H

H	L
4.3	2.95
4.5	3.45
5.0	3.95
5.5	4.45
6.0	4.95
6.5	5.45
7.0	5.95
7.5	6.45
8.0	6.95
8.5	7.45
9.0	7.95
9.5	8.45
10.0	8.95

操作力: $E=250 \pm 50\text{gf}$

PCB. 焊接图

					TOLERANCE							
					UNLESS SPECIFIED							
7	FRAME	BRASS	1	Sn-Plated	UP TO 5mm:	± 0.1	ANGULAR	1				
6	TERMINAL	BRASS	2	Ag-Plated	ABOVE 5mm:	± 0.2	$\pm 1^\circ$		NO	DATE	REVISIONS	
5	CASE	PPA	1	BLACK	TITLE: TACT SWITCH					UNIT : MM	ROHS	DWN
4	REED	SYS301	1	Ag-Plated	MODEL: TC-00100FSA-070E					SCALE: 1:1	COMPLIANT	CHK'D
3	WATERPROOF PAD	RUBBER	1	BLACK								APPD
2	COVER	PPA	1	BLACK								
1	BUTTON	PPA	1	BLACK								
NO.	PART NAME	MATERIAL	QTY	FINISHING								REV :A0