



Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:7A AC/DC

额定电流: 7A AC/DC

Withstanding voltage:1500V

AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃-+85℃

温度范围: -25℃-+85℃

Insulation resistance: 1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X9357 W R - 2xXX EH - LP SW
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:R-Straight 90°
- 4.Row No.Pin No:2xXX-2x04Pin
- 5.Type:EH-The last two holes are connected
- 6.Material:LP-LCP UL94V-0 Black
- 7.Plating:SW-Matte Tin Plated

X9357WR-2XXEH-LPSW	LCP	Brass	X9357HM-EH
PART NO	Material	Material(Pin)	Suitable XKB Housing

广东星坤科技股份有限公司
日期
文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ANGLAR				±5°
L ≤ 4				±0.2
4 < L ≤ 16				±0.3
16 < L ≤ 63				±0.4
L > 63				±0.5

XKIB	DSND	SCALE: N/A	MODEL TYPE:
	DWN	VIEW:	4.2mm Crimp Style Connector
	CHKD	UNIT: mm/in	PART NO.:
	APPD	SIZE: A4	X9357WR-2xXXEH-LPSW
			DWG NO.:
			X-X9357WR-2xXXEH-LPSW
XKIB INDUSTRIAL PRECISION CO., LIMITED		WEIGHT	SHEET
		1/1	REVISION
			A0