


P . C . B LAYOUT



Specifications:

规格:

- Voltage rating:150V AC/DC
- 额定电压: 150V AC/DC
- Current rating:1A AC/DC
- 额定电流: 1A AC/DC
- Withstanding voltage:500V AC/minute
- 耐受电压: 500V AC/分钟
- Temperature range:-25°C~+85°C
- 温度范围: -25°C~+85°C
- Insulation resistance:500MΩ min
- 绝缘电阻: 500MΩ Min
- Contact resistance:30mΩ Max
- 接触电阻: 30mΩ Max

X9862 W V S -XX A -6T SN  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- 1.Series No
- 2.Category :W-Wafer
- 3.Welding Board Angle:V-Straight 180°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:XX-02P-30P
- 6.Special No: A-With Lock
- 7.Material: 6T-PA6T UL94V-0 Beige
- 8.Plating:SN- Tin Plating

Poles	Dimensions(mm)	
	A	B
02	1.25	7.45
03	2.50	8.70
04	3.75	9.95
05	5.00	11.20
06	6.25	12.45
07	7.50	13.70
08	8.75	14.95
09	10.00	16.20
10	11.25	17.45
11	12.50	18.70
12	13.75	19.95
13	15.00	21.20
14	16.25	22.45
15	17.50	23.70
20	23.75	29.95
25	25.00	36.20
30	36.25	42.45

X9862WVS-XXA-6TSN	PA6T	Brass	X9862H-A
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector
DWN	VIEW:	PART NO.: X9862WVS-XXA-6TSN
CHKD	UNIT: mm/in	DWG NO.: X-X9862WVS-XXA-6TSN
APPD	SIZE: A4	



XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

广东星坤科技股份有限公司

Δx	日期
Δx	日期
Δx	日期
MARK	DESCRIPTION

文件工程章

REVISIONS	UNSPECIFIED TOLERANCES
DATE	REVISED
APPROVED	DATE
ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn