

PRODUCT-DETAILS

C2SS1-10B-02

SELECTOR SWITCH C2SS1-10B-02



General Information

Extended Product Type	C2SS1-10B-02
Product ID	1SFA619200R1056
EAN	7320500554746
Catalog Description	SELECTOR SWITCH C2SS1-10B-02
Long Description	Compact Selector Switch - 2-pos Fixed B&C - Short handle - Black - Non-illuminated - Black plastic - 2NC

Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	8536501999

Popular Downloads

Data Sheet, Technical Information	1SFC151007C02__
Instructions and Manuals	1SFC151011M0201

Dimensions

Product Net Width	0.03 m
Product Net Height	0.03 m

Product Net Depth / Length	0.072 m
Product Net Weight	0.024 kg

Technical

Ambient Air Temperature	Operation -25 ... +70 °C Storage -40 ... +85 °C
Color	Black
Actuator Type	Short handle
Bezel Material	Black Plastic
Illumination	Non-illuminated
Function	Maintained
Sub-Function	2-position
Maintained Positions	B, C
Number of Auxiliary Contacts NC	2
Number of Auxiliary Contacts NO	0
Degree of Protection	Front IP66 Front IP67 Front IP69K Terminals IP20
Enclosure Type NEMA	Type1 Type12 Type13 Type3R Type4 Type4X
Pollution Degree	3
Rated Insulation Voltage (U _i)	300 V
Rated Impulse Withstand Voltage (U _{imp})	6 kV
Rated Frequency (f)	50 / 60 Hz
Rated Operational Voltage	Maximum 300 V
Rated Operational Current DC-13 (I _e)	(24 V) 0.3 A (125 V) 0.2 A
Rated Operational Current AC-15 (I _e)	(24 / 127 V) 1.5 A (220 / 240 V) 1 A
Power Loss	Maximum 5 W
Mechanical Durability	0.5 million
Connecting Capacity	Flexible with Ferrule 1 x 0.5...1.5 mm ² Flexible with Ferrule 2 x 0.5...1.5 mm ² Flexible with Insulated Ferrule 1 x 0.5...1.5 mm ² Flexible with Insulated Ferrule 2 x 0.5...1.5 mm ² Flexible 1 x 0.5 ...1.5 mm ² Flexible 2 x 0.5 ...1.5 mm ² Solid 1 x 0.5...1.5 mm ² Solid 2 x 0.5...1.5 mm ²
Terminal Type	Screw Terminals
Tightening Torque	0.8 N·m
Wire Stripping Length	6 mm

Technical UL/CSA

Connecting Capacity	1x 22...14 AWG
UL/CSA	2x 22...14 AWG

Environmental

RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Date	0626 5
RoHS Information	2CMT2015-005451
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business

Certificates and Declarations (Document Number)

CB Certificate	CQC_CN_CN50749
CCC Certificate	2003010305054693_
CQC Certificate	CQC2003010305054693
cURus Certificate	UL_E496500-20171020
Declaration of Conformity - CCC	2020980305001187
Declaration of Conformity - CE	2CMT2015-005451
DNV GL Certificate	9AKK107046A3749
EAC Certificate	RU C-CN.ME77.B.00587/20
Environmental Information	1SAC200022H0002
Instructions and Manuals	1SFC151011M0201
RoHS Information	2CMT2015-005451

Container Information

Package Level 1 Units	bag 10 piece
Package Level 1 Width	0.1 m
Package Level 1 Depth / Length	0.1 m
Package Level 1 Height	0.03 m
Package Level 1 Gross Weight	0.24 kg
Package Level 1 EAN	7320500245460
Package Level 2 Units	10 piece

Classifications

Object Classification Code	S
ETIM 6	EC001029 - Selector switch, complete
ETIM 7	EC001029 - Selector switch, complete
ETIM 8	EC001029 - Selector switch, complete
eClass	V11.0 : 27371243
UNSPSC	39121500
E-Number (Finland)	2312860
E-Number (Norway)	4372692
E-Number (Sweden)	3705533

Categories

Low Voltage Products and Systems → Control Products → Pilot Devices → Compact Range

