

1 ROHS

1 2 3 4 5 6 7 8 9 10

MAPX

MODIFICATION

DRW

DATE

A

A

B

B

C

C

D

D

E





E

F

F

G

G



- NOTES:
 SPECIFICATION:
 1. CURRENT RATING: 3.0A MAX
 2. VOLTAGE: 100 VAC
 3. TEMPERATURE RANGE: -30 °C ~ 85 °C

NO.	DESCRIPTION	MATERIAL	REMARKS	QTY
7	SHELL	塑料 (改性塑料)	BLACK (可印刷)	1PCS
6	SHELL	SPCC	NI Plated	1PCS
5	CONTACT	PCB (镀金/镀银/镀铜)	Au20"	1SET
4	HOUSING	PBT	BLACK	1PCS
3	SHELL	STAINLESS STEEL	NI Plated	1PCS
2	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS

产品图
 PRODUCT CHART DWG
 公差一览表
 TOLERANCE UNLESS OTHERWISE

公差	公差	公差	公差	公差	公差	公差	公差	公差	公差
X	±0.25	X	±5°						
X	±0.20	X	±2°						
XX	±0.05	XX	±1°						
XXX	±0.02	XXX	±0.5°						

深圳市精拓金电子有限公司
 Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位	制图	制图料号	产品名称	转接头	母头	长度	颜色
MM	YANG	917-B88C201AH70204		TYPE-C	0.120	16	黑壳+红铜壳

1 2 3 4 5 6 7 8 9 10