

1 ROHS





2 3 4 5 6 7 8 9 10

MAPX

MODIFICATION

DRW

DATE



NOTES:
SPECIFICATION:
1. CURRENT RATING: 3.0A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C

NO.	DESCRIPTION	MATERIAL	REMARKS	QTY
7	SHELL	塑料 (改性塑料)	BLACK (可印刷)	1PCS
6	SHELL	SPCC	NI Plated	1PCS
5	CONTACT	POB (镀金磷青铜)	Au20"	1SET
4	HOUSING	PBT	BLACK	1PCS
3	SHELL	STAINLESS STEEL	NI Plated	1PCS
2	CONTACT	COPPER ALLOY	Au/"/Ni Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS

产品图
PRODUCT CHART DWG

公差一览表
TOLERANCE UNLESS OTHERWISE

公差	公差一覽表	公差一覽表	公差一覽表	公差一覽表	公差一覽表	公差一覽表	公差一覽表	公差一覽表	公差一覽表	公差一覽表
X	±0.25	X	±5°	MM						
X	±0.20	X	±2°	1:1	1:1	1:1	1:1	1:1	1:1	1:1
XX	±0.05	XX	±1°	DATE						
XXX	±0.02	XXX	±0.5°	2020-05-22	2020-05-22	2020-05-22	2020-05-22	2020-05-22	2020-05-22	2020-05-22

单位: MM
比例: 1:1
日期: 2020-05-22

制图: YANG
审核: 郭裕富
核准: 黄国荣

制图料号: 917-B88C101AH70200
产品名: 转换器
角法: 第三角

版本: AD

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

ROHS