

1 ROHS




1 2 3 4 5 6 7 8 9 10

MAPX

MODIFICATION

DRW

DATE

- NOTES:  
 SPECIFICATION:  
 1. CURRENT RATING: 3.0A MAX  
 2. VOLTAGE: 100 VAC  
 3. TEMPERATURE RANGE: -30 °C ~ 85 °C

NO.	DESCRIPTION	MATERIAL	REMARKS	QTY
7	SHELL	塑料 (改性塑料)	BLACK (可印刷)	1PCS
6	SHELL	SPCC	NI Plated	1PCS
5	CONTACT	PCB (镀金/镀银/镀铜)	Au20"	1SET
4	HOUSING	PBT	BLACK	1PCS
3	SHELL	STAINLESS STEEL	NI Plated	1PCS
2	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS

产品图  
 PRODUCT CHART DWG  
 公差一览表  
 TOLERANCE UNLESS OTHERWISE

公差	公差								
X	±0.25	X	±5°	X	±5°	X	±5°	X	±5°
X	±0.20	X	±2°	X	±2°	X	±2°	X	±2°
XX	±0.05	XX	±1°	XX	±1°	XX	±1°	XX	±1°
XXX	±0.02	XXX	±0.5°	XXX	±0.5°	XXX	±0.5°	XXX	±0.5°

深圳市精拓金电子有限公司  
 Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位	UNIT	MM	制图	DRAWING	YANG	制图料号	PRODUCT PART NO.	917-B88C201AH70203
比例 <td>SCALE</td> <td>1:1</td> <td>审核 <td>CHECK</td> <td>郭裕富</td> <td>产品名称 <td>PRODUCT NAME</td> <td>转接TYPE-C母头转USB-A母头</td> </td></td>	SCALE	1:1	审核 <td>CHECK</td> <td>郭裕富</td> <td>产品名称 <td>PRODUCT NAME</td> <td>转接TYPE-C母头转USB-A母头</td> </td>	CHECK	郭裕富	产品名称 <td>PRODUCT NAME</td> <td>转接TYPE-C母头转USB-A母头</td>	PRODUCT NAME	转接TYPE-C母头转USB-A母头
日期 <td>DATE</td> <td>2020-05-22</td> <td>核准 <td>APPRO</td> <td>黄国荣</td> <td>角法 <td>VIEW</td> <td>第三角</td> </td></td>	DATE	2020-05-22	核准 <td>APPRO</td> <td>黄国荣</td> <td>角法 <td>VIEW</td> <td>第三角</td> </td>	APPRO	黄国荣	角法 <td>VIEW</td> <td>第三角</td>	VIEW	第三角
								版本
								AD

1 2 3 4 5 6 7 8 9 10

G F E D C B A