

1 2 3 4 5 6 7 8 9 10

ROHS

12.00

12.02


15.00

7.10

20.00

7.98

4.50



MAPX

MODIFICATION

DRW

DATE

- NOTES:
 SPECIFICATION:
 1. CURRENT RATING: 3.0A MAX
 2. VOLTAGE: 100 VAC
 3. TEMPERATURE RANGE: -30 °C ~ 85 °C

| NO. | DESCRIPTION | MATERIAL | REMARKS | QTY |
|-----|-------------|--------------------------|--------------|------|
| 7 | SHELL | 塑料 (改性塑料) | BLACK (可印刷) | 1PCS |
| 6 | SHELL | SPCC | NI Plated | 1PCS |
| 5 | CONTACT | PCB (镀金铜线电阻) | Au20" | 1SET |
| 4 | HOUSING | PBT | BLACK | 1PCS |
| 3 | SHELL | STAINLESS STEEL | NI Plated | 1PCS |
| 2 | CONTACT | COPPER ALLOY | Au/Ni Plated | 1SET |
| 1 | HOUSING | HIGH TEMPERATURE PLASTIC | BLACK | 1PCS |

产品图
 PRODUCT CHART DWG

公差一览表
 TOLERANCE UNLESS OTHERWISE

| 公差 | 标注 | 公差 | 角度 |
|-----|-------|-----|-------|
| X | ±0.25 | X | ±5° |
| X | ±0.20 | X | ±2° |
| XX | ±0.05 | XX | ±1° |
| XXX | ±0.02 | XXX | ±0.5° |

深圳市精拓金电子有限公司
 Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位: MM
 比例: 1:1
 日期: 2020-05-22

制图: YANG
 审核: 郭裕富
 核准: 黄国荣

制图料号: 917-B88C101AH70202
 产品名称: 转接头TYPE-C母头转USB-A母头
 角法: 第三角
 版本: AD