



LOGO D/C



NO	NAME	MATERIAL	PLATING	COLOR
10	COVER2	PAGE+30%G.F, U194V-0		BLUE
9	COVER1	PAGE+30%G.F, U194V-0		BLUE
8	4PORT HOUSING	PAGE+30%G.F, U194V-0		BLUE
7	3PORT HOUSING	PAGE+30%G.F, U194V-0		BLUE
6	HOUSING	PAGE+30%G.F, U194V-0		BLUE
5	MIDDLE BULLET	SK7 T=0.25	60u"Nickel Plated & 50u"Copper Plated	
4	BACK SHELL	SUS304 T=0.25		
3	SHELL	SUS430 T=0.25	60u"MIN MATTE TIN PLATING ON SOLDER TAILS OVER 50u"MIN NICKEL.	
2	USB3.0 CONTACTS (1,2,3,4,5PORT)	Copper Alloy	Au1u" & 100u"Matte Tin Plated & 50u"Nickel Plated	
1	USB2.0 CONTACTS (1,2,3,4PORT)	Copper Alloy	Au1u" & 100u"Matte Tin Plated & 50u"Nickel Plated	

# 深圳市精拓金电子有限公司

产品图

公差一览表

公差	公差	公差	公差
X	±0.35	X	±5°
X	±0.30	X	±2°
XX	±0.20	XX	±1°
XXX	±0.10	XXX	±0.5°

单位	MM	制图	GAVIN	制料号	907-113A105CD10200
比例	1:1	审核	郭治富	产品名称	4口3.0速度即层弯脚边平焊不锈钢406盘款300C
日期	2016-09-09	核准	黄国荣	角法	
DATE		APPD		版本	A0

MAPX	MODIFICATION	DATE