



- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
  2. 温度范围: -25°C ~ 85°C。
  3. 额定电压: 100V, AC/DC。
  4. 接触电阻: ≤ 0.02Ω。
  5. 绝缘电阻: ≥ 500MΩ。
  6. 额定电流: 1A, AC/DC。

CKT	DIM A	DIM B
2	1.50	6.00
3	3.00	7.50
4	4.50	9.00
5	6.00	10.50
6	7.50	12.00
7	9.00	13.50
8	10.50	15.00
9	12.00	16.50
10	13.50	18.00
11	15.00	19.50
12	16.50	21.00
13	18.00	22.50
14	19.50	24.00
15	21.00	25.50
16	22.50	27.00
17	24.00	28.50
18	25.50	30.00
19	27.00	31.50
20	28.50	33.00

DEALON 德之隆  
ELECTRONICS CO., LTD

APPROVALS

APPROVALS	DATE
DRAWN G.M.Chen	2015/7/17
CHECKED	
APPROVALS	

TOLERANCES ARE

30~30	±0.30	ANGLE
10~30	±0.20	
0~10	±0.15	
~5	±0.10	

PART NO. ZH-XXPS  
UNIT: mm SCALE: 1:1 SHEET 1 OF 1  
DRAWING NO. PROJ.

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			