

	1	2	3	4	5	6	7	8	9	10																																																																										
	环保物料		物料明细表 Material list				TEL:0769-82001899																																																																													
A	序号 NO.	部件 PARTS	线材、端子、(部件) 胶壳 Cable, Terminal (Part) Housing			数量 Quantity	技术要求: 1. 1. 端子铆接牢固, 无松动, 脱落现象; 1. 2. 线材印字清晰, 无破损划伤; 2. 外观要求按品质管理部检验标准执行 3. 包装要求按包装作业指引或者客户制定包装要求																																																																													
	①	胶壳	P2501-06 XFCN 兴飞			1PCS																																																																														
	②	端子	T2501PS-2 XFCN 兴飞			6PCS																																																																														
	③	线材	红白排线2468 26AWG, 6P			1PCS																																																																														
B																																																																																				
C																																																																																				
D																																																																																				
E																																																																																				
F																																																																																				
G	<table><tr><td></td><td></td><td></td><td></td><td colspan="2">TOLERANCE UNLESS OTHERWISE</td><td>DRAWN</td><td>CK tan</td><td colspan="2">XFCN 兴飞连接器有限公司</td><td>SHEET</td><td>1/1</td></tr><tr><td></td><td></td><td></td><td></td><td colspan="2">X. ±0.3 X° ±5°</td><td>CHKD</td><td></td><td colspan="2">XFCN CONNECTORS CO., LTD.</td><td>DATE</td><td>2022. 8. 10</td></tr><tr><td></td><td></td><td></td><td></td><td colspan="2">. X ±0.20 . X° ±2°</td><td>APPD</td><td></td><td colspan="2">PRODUCT NAME</td><td>UNITS</td><td>mm</td></tr><tr><td></td><td></td><td></td><td></td><td colspan="2">. XX ±0.08 . XX° ±1°</td><td></td><td></td><td colspan="2">XH2.5mm端子线UL2468 26# 单头镀锡 L=200mm 6P</td><td>SCALE</td><td></td></tr><tr><td>A0</td><td colspan="3">MODIFICATION</td><td>DRAW</td><td>DATE</td><td colspan="2">VIEW</td><td>⊕</td><td>PART. NO.</td><td>XF-P00033</td><td>DWG NO.</td><td></td></tr><tr><td>AVR</td><td colspan="3"></td><td></td><td></td><td colspan="2"></td><td></td><td colspan="2"></td><td colspan="2"></td></tr></table>														TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN 兴飞连接器有限公司		SHEET	1/1					X. ±0.3 X° ±5°		CHKD		XFCN CONNECTORS CO., LTD.		DATE	2022. 8. 10					. X ±0.20 . X° ±2°		APPD		PRODUCT NAME		UNITS	mm					. XX ±0.08 . XX° ±1°				XH2.5mm端子线UL2468 26# 单头镀锡 L=200mm 6P		SCALE		A0	MODIFICATION			DRAW	DATE	VIEW		⊕	PART. NO.	XF-P00033	DWG NO.		AVR												
				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN 兴飞连接器有限公司		SHEET	1/1																																																																									
				X. ±0.3 X° ±5°		CHKD		XFCN CONNECTORS CO., LTD.		DATE	2022. 8. 10																																																																									
				. X ±0.20 . X° ±2°		APPD		PRODUCT NAME		UNITS	mm																																																																									
				. XX ±0.08 . XX° ±1°				XH2.5mm端子线UL2468 26# 单头镀锡 L=200mm 6P		SCALE																																																																										
A0	MODIFICATION			DRAW	DATE	VIEW		⊕	PART. NO.	XF-P00033	DWG NO.																																																																									
AVR																																																																																				
	1	2	3	4	5	6	7	8	9	10																																																																										