

NOTES1:

UL Standard

- 1.Rated voltage/current : 300V / 15A
- 2.Withstanding voltage : AC1600V/1Min.

IEC Standard

1. Pollution degree	2
Overvoltage category	III
Rate impulse voltage(KV)	4KV
Rate voltage(V)	320V
Rate current(A)	10A

NOTES2:

- 1.Dimension shall be interpreted per ASME Y14.5-2009
- 2.Pitch : 5.08mm, Poles : N=04~48P
- 3.Operating temperature:-40°C~+105°C
- 4.Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm						
TO	Over	TO	Over	TO	Over	TO	Over	0.1/10
6	6	10	10	24	30	30	60	100
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2'

5.RoHS Compliance

Ordering Information

JL2EDGRT - 508 XX G 0 1






Pitch
508=5.08PH

No.of pins
4P~48P

Housing Color
B=Black
G=Green
U=Blue
R=Red
W=White
Y=Yellow
□=Orange
E=Grey

Packing
0=Pe bag
T=Tube
A=Tray

2x13(含) 以上本体需要左右拼接



PCB LAYOUT

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE

DRAW	SHUANGPING ZHENG	SCALE	FIT	JILN ® 东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO.,LTD	
		UNIT	mm		
CHECK	LICHAD LIU	SIZE	A4	PART NO.	JL2EDGRT-508XXG01
		SHEET	1/1	TITLE:	JL2EDGRT-5.08-2xNP插拔式公座/弯脚/开口/绿色
APPROVE	TONGLIANG GAO	PROJ.			