







- 1>.Operating force:1000gf Max  
 2>.Operating Temperature:-40° to+85°  
 3>.Storage Temperature: -40° to+85°  
 4>.Electrical life Life:2000cycles 25mA 24VDC  
 5>.Mechanical Life:3000cycles Operations

2. PLATING:  
 GOLD FLASH 1u"~2u" SOLDER TAIL,  
 1u"~3u" GOLD PLATING ON THE CONTACT AREA,  
 WITH 50u" NICKEL UNDERPLATING OVERALL.

3. PART NUMBER DESCRIPTION :  
 DSHP XX T J G E T  
 [包装方式: T=管装 R=Reel]  
 [电镀层: E=接触部 1u"~3u" 焊脚部 1u"~2u" ]  
 [G=镀金 S=内镀金(接触部)外镀锡(焊脚部)]  
 [脚型: S脚 / J脚 / H脚 / A脚 / Z脚]  
 [T=低推贴胶 S=低推不贴胶 L=长推]  
 [产品数: 02=2P 04=4P ..... 08=8P 10=10P ]



Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Beryllium Copper	1u"~3u" Gold
④	Terminal	Brass	1u"~2u" Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	1u"~3u" Gold
⑦	Mylar	UL94 V0	0.05mm

RECOMMENDED P.C.B. LAYOUT (TOP VIEW)

TOLERANCE UNLESS OTHERWISE SPECIFIED	INSPECTION COPY
LINER	ANGLES
.0 ± 0.25	0. ± 2'
.00 ± 0.15	.0 ± 1'
.000± 0.10	.00± 0.5'
DESIGN	kathy
DRAWING	03/20/12'
CHECK	
APPRO.	

DongGuan Kingtek Industrial Co., Ltd.			
TITLE			
BY DSHP SERIES PITCH 1.27mm			
PRODUCT FAMILY DSHP SERIES			
PRAT NO. DSHP08TJGET			
FILE NO. DSHP08TJGET-A			
SIZE	UNIT	SCALE	SHEET
A4	mm	2 : 1	1 OF 1
REV.			
A			