


REV.	ECN. NO.	APPD.
A		

NOTES:
 Current Rating:3.0AMP
 Contact Resistance:20mΩ max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ min
 Operation Temperature:-40℃ to +105℃

Contact Material:Brass
 Contact plating:Au or Sn Over Ni
 Insulator Material:PBT or PA6T+30%GF(UL94V-0)





Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)




MTP125-11XXS1- X


No.of Pins per
 Row: 01~40

Colour
 R : red
 Y : yellow
 W : white
 G : green
 B : blue



Dimension antitheses list		
ITEM	A	B
Standard	3.00	6.00
Alternate		

X. ± 0.30	X°. ± 5°	UNITS mm	NAME(INTENDED USE)		MINTRON CO.,LTD.			
.X ± 0.20	.X°. ± 2°	MAT'L	PART NO.(INTENDED USE)		TITLE: MTP125-11XXS1-X			
.XX ± 0.10	.XX°. ± 1°		APPD: SUNNY		DWG NO.:			
.XXX ± 0.05	.XXX°. ± 0.5°	FINISH	CHKD: LISA					
PIN HEADER CONNNECTOR		Q'TY	DR: ZOE 2006-11-28					
					SCALE SHEET REV.			
					1 / 1 1 / 1 A			



SCALE	SHEET	REV.
1/1	1/1	A