



REV.	ECN. NO.	APPD.
A		

NOTES:
Rated Current:2.0AMP.
Contact Resistance:20mΩ Max.
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min.
Operation Temperature:-40℃ to +105℃

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:PA9T+30%G.F UL94V-0 BK





Recommended P.C.B Layout (Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

MTP220-11XXR1

No.of Pins per
Row: 01~40



Item	Pin Length	A	D	B	Mating
Standard	10.50	2.80	0.75	4.00	2240 2243 2263 2272
Alternate					

X. ± 0.30	X.° ± 5°	UNITS mm	NAME(INTENDED USE)		MINTRON CO.,LTD.				
.X ± 0.20	.X° ± 2°	MAT'L							
.XX ± 0.10	.XX° ± 1°	FINISH	PART NO.(INTENDED USE)		TITLE: MTP220-11XXR1				
.XXX ± 0.05	.XXX° ± 0.5°								
PIN HEADER CONNECTOR		Q'TY	APPD: SUNNY		DWG NO.:				
			CHKD: LISA						
			DR: ZOE 2006-11-28						
							SCALE 1 / 1	SHEET 1 / 1	REV. A