



REV.	ECN. NO.	APPD.
A		

NOTES:
Current Rating:1.5AMP
Contact Resistance:20mΩ max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ min
Operation Temperature:-40℃ to +105℃

Contact Material:Brass
Contact plating:Au or Sn Over Ni
Insulator Material:PA6T or PBT+30%GF(UL94V-0)
Contact Plated:Gold Flash





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)




MTP220-12XXS1

No.of Pins per
Row: 01~40



Dimension antitheses list		
ITEM	A	B
Standard	2.80	4.00
Alternate		

X. ± 0.30	X°. ± 5°	UNITS mm	NAME(INTENDED USE)	MINTRON CO.,LTD.			
.X ± 0.20	.X°. ± 2°	MAT'L					
.XX ± 0.10	.XX°. ± 1°	FINISH	PART NO.(INTENDED USE)	TITLE: MTP220-12XXS1			
.XXX ± 0.05	.XXX°. ± 0.5°		Q'TY	APPD: SUNNY	DWG NO.:		
PIN HEADER CONNECTOR			CHKD: LISA				
			DR: ZOE 2006-11-28		SCALE 1 / 1	SHEET 1 / 1	REV. A



SCALE	SHEET	REV.
1/1	1/1	A