



REV.	ECN. NO.	APPD.
A		

NOTES:
 Current Rating:3.0AMP
 Contact Resistance:20mΩ max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ min
 Operation Temperature:−40℃ to +105℃



Contact Material:Brass
 Contact plating:Au or Sn Over Ni
 Insulator Material:PBT or PA6T+30%GF(UL94V−0)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



MTP220-11XXS1

No.of Pins per
 Row: 01~40



Dimension antitheses list		
ITEM	A	B
Standard	2.80	4.00
Alternate		

X. ± 0.30	X.° ± 5°	UNITS mm	NAME(INTENDED USE)	MINTRON CO.,LTD.		
.X ± 0.20	.X° ± 2°	MAT'L	PART NO.(INTENDED USE)			
.XX ± 0.10	.XX° ± 1°	FINISH	APPD: SUNNY	TITLE: MTP220-11XXS1		
.XXX ± 0.05	.XXX° ± 0.5°	Q'TY	CHKD: LISA			
PIN HEADER CONNECTOR			DR: ZOE 2006-11-28	DWG NO.:		
					SCALE 1/1	SHEET 1/1
					REV. A	