




项目	零件名称	数量	材质	处理/备注
1	SHELL	1	STAINLESS	Ni:50u"
2	Molding HOUSING	2	L.C.P	(Black)
3	GND SPRING	2	STAINLESS	Ni:50u"
4	Insert molding 12PIN	2	L.C.P	(Black)
5	CONTACT	24	COPPER ALLOY	Contact area: gold flash, Solder tails: Tm100u", Ni:50u"
6	PCB	1		




**SPECIFICATION MATERIAL**

See drawing  
**STANDARD DATA**  
 Operating temperature: -10°C ~ +60°C  
 Storage temperature: -20°C ~ +85°C  
**ELECTRICAL**

Insulator resistance: 100Mohms Min.  
 Withstanding voltage: 100 VAC / minute  
 Contact resistance: initial 40ohms Max;  
 after 50ohms Max.

**MECHANICAL**

Mating force: 5~20N  
 Umating force : 8~20N  
 Durability: 5000 cycles Min.



C1: A5, B5, A9, B9  
 R2: A9, B9, A12, B12  
 R1: A12, B12/外壳+卡勾

**产品图**  
 PRODUCT CHART DWG

**深圳市精拓金电子有限公司**

公差一览表 TOLERANCE UNLESS OTHERWISE		单位 UNITS	MM	制图 DRAWING	Z-Y-B	产品料号 PRODUCT PART NO.	918-128A2021A30322
X	±0.25	X'	±5'	审核		产品名称	
.X	±0.20	.X'	±2'	核准		角法	
.XX	±0.15	.XX'	±1'			版本	A0
.XXX	±0.10	.XXX'	±0.5'			日期	2022.09.06

