



RECOMMEND P.C.B LAYOUT(COMPONENT SIDE)
TOLERANCE FOR PCB LAYOUT IS ±0.05



装前塞示意图

USB TYPE C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A5	CC1	B9	VBUS
A9	VBUS	B5	CC2
A12	GND		

- 备注 (NOTE):
- 电气特性:
 - 接触区: 接触电阻40mΩ Max, 允许10mΩ变化量. 测试条件: 20mv, 100mA下测量.
 - 接触电流: 3A VBUS引脚; 1.25A用于GND引脚; 其他引脚为0.25A.
 - 额定电压: 5V.
 - 耐受电压: 100VAC.
 - 绝缘电阻: 至少100兆欧.
 - 机械性能:
 - 插入力: 0.5-2.0Kg
 - 拔出力: 0.6-2.04Kg
 - 插拔次数: 10000次.
 - 工作环境: -20°C to +85°C.

TABLE:

NO	PART	QTY	Material
1	SHELL	1	STAINLESS STEEL,NI PLATED
2	CONTACT	6	COPPER STEEL,TIN/AU/NI PLATED
3	1MD HOUSING	1	HIGH TEMPERATURE RESISTANT PLASTIC BLACK UL94 V-0
4	2MD HOUSING	1	HIGH TEMPERATURE RESISTANT PLASTIC BLACK UL94 V-0

产品图

深圳市精拓金电子有限公司

公差一览表		制图		制图料号	
TOLERANCE	UNLESS OTHERWISE	UNITS	MM	PRODUCT PART NO	918-4688K2028Y10000
X	±0.15	X	±5°	审核	郭治富
X	±0.10	X	±2°	审核	郭治富
XX	±0.05	XX	±1°	核准	黄国荣
XXX	±0.03	XXX	±0.5°	DATE	2016-09-09





MAPX

MODIFICATION

DATE

1 2 3 4 5 6 7 8 9 10

MAPX	MODIFICATION	DATE
------	--------------	------



CONNECTOR (PCS)	REEL	CARTON
	600	6000

产品图
PRODUCT CHART DWG
公差一览表
深圳市精拓金电子有限公司

TOLERANCE UNLESS OTHERWISE	公差一览表	UNIT	MM	DRAWING	2-Y-B	PRODUCT PART NO.	
X ±0.15	X	±5°		审核	郭治富	产品名称	TYPE C 8P 立插防水母座(Φ=8mm (E款))
X ±0.10	X	±2°	1:1	CHD	黄国荣	PRODUCT NO.	-包装规范
XX ±0.05	XX	±1°	DATE	APPD		角法	版本
XXX ±0.03	XXX	±0.5°	2016-09-09			VER	AD

G 1 2 3 4 5 6 7 8 9 10 G

F 1 2 3 4 5 6 7 8 9 10 F

E 1 2 3 4 5 6 7 8 9 10 E

D 1 2 3 4 5 6 7 8 9 10 D

C 1 2 3 4 5 6 7 8 9 10 C

B 1 2 3 4 5 6 7 8 9 10 B

A 1 2 3 4 5 6 7 8 9 10 A