

PRODUCT NO.	1
DSIC03THGET	RoHS compliant

REV.	ECN NO.	DR	DATE


- NOTES :
- 1.Specification:
 1>.Operating force:1000gf Max
 2>.Operating Temperature: -40° to+85°
 3>.Storage Temperature: -40° to+85°
 4>.Mechanical Life:3000cycles minimum
 5>.Electrical Life:2000cycles 25mA 24VDC
 2. PLATING:
 GOLD FLASH 1u"~2u"SOLDERTAIL,
 1u"~3u" GOLD PLATING ON THE CONTACT AREA,
 WITH 50u" NICKEL UNDERPLATINGOVERALL.

3. PART NUMBER DESCRIPTION






DSIC XX T H G E T

- [包装方式: T=管装 R=Reel]
- [电镀层:E=接触部1u"~3u" /焊尾部1u"~2u"]
- [G=镀金 S=内金外镀]
- [脚型: S脚 / J脚 / B脚 / A脚 / Z脚]
- [T=低推贴胶 S=低推不贴胶 L=长推]
- [产品数:01=1P 03=3P 12=12P]


[Schematic]



[推钮行程]



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



Number	Part Name	Material	Finished	TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	 东莞市广普实业有限公司 DongGuan Kingtek Industrial Co., Ltd.										
①	Actuator	UL94 V0	White	LINER	ANGLES	PROJECTION 											
②	Cover	UL94 V0	Black	.0 ± 0.25	0. ± 2°												
③	Movable	Copper Alloy	1u"~3u"Gold	.00 ± 0.15	.0 ± 1°												
④	Terminal	Brass	1u"~2u"Gold	.000± 0.10	.00± 0.5°	2012/04/12		TITLE BY DSIC SERIES PITCH 2.54mm									
⑤	Base	UL94 V0	Black	DESIGN	kathy			PRODUCT FAMILY DSIC SERIES									
⑥	Terminal Contact	Brass	1u"~3u"Gold	DRAWING				PRAT NO. DSIC03THGET									
⑦	Marly	UL94 V0	0.05mm	CHECK			FILE NO. DSIC03THGET-A										
				APPRO.			<table><tr><th>SIZE</th><th>UNIT</th><th>SCALE</th><th>SHEET</th><th>REV.</th></tr><tr><td>A4</td><td>mm</td><td>2 : 1</td><td>1 OF 1</td><td>A</td></tr></table>	SIZE	UNIT	SCALE	SHEET	REV.	A4	mm	2 : 1	1 OF 1	A
SIZE	UNIT	SCALE	SHEET	REV.													
A4	mm	2 : 1	1 OF 1	A													