




PRODUCT NO.	1	2	3	4	5	6
DSIC04LSGER	RoHS compliant					

REV.	ECN NO.	DR	DATE



- NOTES :
- 1.Specification:
 1>.Operating force:1000gf Max
 2>.Operating Temperature: -40° to+85°
 3>.Storage Temperature: -40° to+85°
 4>.Mechanical Life:3000cycles minimum
 5>.Electrical Life:2000cycles minimum
 2. PLATING:
 GOLD FLASH 1u"~2u" SOLDER TAIL,
 1u"~3u" GOLD PLATING ON THE CONTACT AREA,
 WITH 50u" NICKEL UNDERPLATING OVERALL.

3. PART NUMBER DESCRIPTION


DSIC	XX	L	S	G	E	R	
							[包装方式: T=管装 R=Reel]
							[电镀层: E=接触部 1u"~3u" /焊接部 1u"~2u"]
							[G=镀金 S=内金外镍]
							[脚型: S脚 / J脚 / H脚 / A脚 / Z脚]
							[T=低推贴胶 S=低推不贴胶 L=长推]
							[产&P数: 02=2P 08=8P 10=10P 12=12P]



[Schematic]




RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



[推钮行程]

(Construction)



Number	Part Name	Material	Finished	TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	PROJECTION	DRAWING CHECK APPRO.	FILE NO.	SIZE	UNIT	SCALE	SHEET	REV.
				LINER	ANGLES									
①	Actuator	UL94 V0	White	.0 ± 0.25	0. ± 2°				DSIC04LSGER-A	A4	mm	2 : 1	1 OF 1	A
②	Cover	UL94 V0	Black	.00 ± 0.15	.0 ± 1°									
③	Movable	Copper Alloy	1u"~3u"Gold	.000± 0.10	.00± 0.5°									
④	Terminal	Brass	1u"~2u"Gold											
⑤	Base	UL94 V0	Black											
⑥	Terminal Contact	Brass	1u"~3u"Gold											

东莞市广普实业有限公司
DongGuan Kingtek Industrial Co., Ltd.

TITLE	BY DSIC SERIES PITCH 2.54mm
PRODUCT FAMILY	DSIC SERIES
PRAT NO.	DSIC04LSGER
FILE NO.	DSIC04LSGER-A
SIZE	A4
UNIT	mm
SCALE	2 : 1
SHEET	1 OF 1
REV.	A