

PRODUCT NO.	RoHS compliant
DSWB07LHGETR	

REV.	ECN NO.	DR	DATE

Note:

- All dimensions are in millimeters.
- General tolerance: $\pm 0.2\text{mm}$.
- Material:

Base: UL94V-0 PBT Thermoplastic (Black).
 Cover: UL94V-0 PBT Thermoplastic (Black/Red/Blue).
 Actuators: UL94V-0 PBT Thermoplastic (White).
 Contact plating: Gold plating over nickel.
 Pitting material: Epoxy.



4. Electrical

Electrical: 2000 Operations per switch 24/VDC, 25mA.
 Non-Switching Rating: 100mA, 50/VDC.
 Switching Rating: 25mA, 24/VDC
 Contact Resistance: 100 mΩ Max. at initial.

5. Mechanical

Mechanical life: 2000 Operations per switch.
 Stroke: 2.0mm.
 Operation Temp: -20°C to 70°C.
 Storage Temp: -40°C to 85°C.

6. PART NUMBER DESCRIPTION:



注意:

- 波峰焊: 推荐焊锡温度在 $270^{\circ}\text{C} \pm 5^{\circ}\text{C}$, 浸锡时间为 5~6 秒钟。
- 手工焊: 使用 30 瓦烙铁控制温度在 320°C , 焊接时间大约 2~3 秒钟。
- 拨柄位置: 产品焊接时, 请将产品的拨柄置于 OFF 端, 能给予产品更好的接触性能。
- 清洗过程: 清洗使用超声波方式, 能给予更好的效果。

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	 东莞市广誉实业有限公司 DongGuan Kingtek Industrial Co., Ltd.
LINER	ANGLES	PROJECTION	
.0 ± 0.30	0. ± 1'		TITLE
.00 ± 0.20	.0 ± 0.5'		BY DSWB SERIES PITCH 2.54mm
.000± 0.10	.00±	PRODUCT FAMILY DSWB SERIES	
DESIGN	LU ER XIN	2013/07/02	PRAT NO. DSWB07LHGETR
DRAWING			FILE NO. DSWB07LHGETR-A
CHECK			SIZE UNIT SCALE SHEET REV.
APPRO.			A4 mm FIT 1 OF 1 A