



MAPX	MODIFICATION	DATE
------	--------------	------

- 备注:
- 1.材质:
 - 1.1扣套: 黑色 LCP+20%G.F UL94V-0
 - 1.2端子: 黄铜 C2680-H, T=0.15mm; 镀半金锡足1U"
 - 1.3外壳: 不锈钢 SUS201, T=0.15mm; 表面镀珍珠镍
 - 1.4卡钩: 不锈钢 SUS201, T=0.30mm
 - 1.5PCB: FR4 喷锡
 - 2.主要特性:
 - 2.1额定电流: 3A
 - 2.2接触阻抗: 40mΩ MAX
 - 2.3绝缘阻抗: 100MΩ MIN 250V DC
 - 2.4耐压测试: 300V AC
 - 2.5沾锡性: 温度25±5℃
 - 2.6整体插入力: 3.57kgf MAX
 - 2.7使用寿命: 10000次
 - 2.8工作温度: -30℃~+85℃

R1: 56KΩ±5% 0402
 R2: 空
 R3: 空
 C1: 空

A12	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1
GND	RX2+	RX2-	Vbus	SUB1	D-	D+	CC1	Vbus	TX1-	TX1+	GND
GND	TX2+	TX2-	Vbus	CC2	D+	D-	SUB2	Vbus	RX1-	RX1+	GND
B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12

产品图
PRODUCT CHART DWG

深圳市精拓金电子有限公司

公差一览表 TOLERANCE UNLESS OTHERWISE SPECIFIED		单位 UNITS	MM	制图 DRAWING	尹先华	制料号 PRODUCT PART NO.	918-248N2022AW42002
X	±0.30	X	±5°	审核 CHKD	郭治富	产品名称 PRODUCT NO.	TYPE-C3.1公头10.6/15.7拉伸款
X	±0.25	X	±2°	核准 APPD	黄国荣	四焊盘R56k数据充电24PIN黑胶	
XX	±0.15	XX	±1°	日期 DATE	2017-05-12	角法 VIEW	版本 VER
XXX	±0.10	XXX	±0.5°				AD