



Recommended PCB Layout(Top view)  
Tolerance:±0.05mm

Specifications:

规格:  
Voltage rating:125V AC/DC  
额定电压: 125V AC/DC  
Current rating:1A AC/DC  
额定电流: 1A AC/DC  
Withstanding voltage:500V AC/minute  
耐受电压: 500V AC/分钟  
Temperature range:-25°C~+105°C  
温度范围: -25°C~+105°C  
Insulation resistance:≥100MΩ  
绝缘电阻: ≥100MΩ  
Contact resistance:≤20mΩ  
接触电阻: ≤20mΩ

X9821 W V - XX R - LP SN  
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Straight 180°
- 4.Row No.Pin No:XX-02~16Pin
- 5.Special No:R-DIP 2.3mm
- 6.Material:LP-LCP UL94V-0 ,Natural  
CAP:LCP UL94V-0 ,Natural
- 7.Plating:SN- Tin Plated



Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B	C		A	B	C
02	1.25	3.20	4.25	10	11.25	13.20	14.25
03	2.50	4.45	5.50	11	12.50	14.45	15.50
04	3.75	5.70	6.75	12	13.75	15.70	16.75
05	5.00	6.95	8.00	13	15.00	16.95	18.00
06	6.25	8.20	9.25	14	16.25	18.20	19.25
07	7.50	9.45	10.50	15	17.50	19.45	20.50
08	8.75	10.70	11.75	16	18.75	20.70	21.75
09	10.00	11.95	13.00				

X9821WW-XXR-LPSN	LCP	Brass	X9821HM
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector
DWN		VIEW:	PART NO.: X9821WW-XXR-LPSN
CHKD		UNIT: mm/in	DWG NO.: X-X9821WW-XXR-LPSN
APPD		SIZE: A4	

广东星坤科技股份有限公司

日期

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED
	REVISIONS			

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0