



Poles	Dimensions(mm)		Dimensions(mm)	
	A	B	A	B
02	2.00	6.00	08	14.00
03	4.00	8.00	09	16.00
04	6.00	10.00	10	18.00
05	8.00	12.00	11	22.00
06	10.00	14.00	12	24.00
07	12.00	16.00	13	26.00
				28.00

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25° C~85° C.
3. 额定电压: 50V, AC, DC.
4. 接触电阻: ≤0.02Ω.
5. 绝缘电阻: ≥100MΩ

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/7/17	PH-D-XXA	
CHECKED			SHEET 1 OF 1	
APPROVALS			PROJ.	
TOLERANCES ARE: 30~40L ±0.30 ANGLE ±2° 10~30 ±0.20 UNIT: mm SCALE: 1:1 5~10 ±0.15 ±2° DRAWING NO.				
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.
	A		NEW	

DEALON 德之隆
ELECTRONICS CO.,LTD

2.0 Pitch 直插