





CAD FILE:

Technical Data
Material:
Contact material:Phosphor bronze
Plating:Gold Flash
Insulator material:Black polyester UL94V-0
Standard:PA6T+30%G.F

Electrical:
Current rating:1.0Amps/contact max.
Contact resistance: $\leq 20m\Omega$ /contact
Insulation resistance: $\geq 1000M\Omega$ at V=100V
Withstanding voltage:300V AC/minute

Mechanical:
Soldering temperature:+260℃,4s max
UNSPECIFIED TOLERANCE: ± 0.20



PCB Layout

$$A=1.27*\frac{nP}{2}+0.4\pm 0.35$$

$$B=1.27*\frac{nP}{2}-1.27\pm 0.2$$

Pin Number=2~100

							APPROVALS		DATE		DEALON德之隆® ELECTRONICS CO.,LTD		
							DRAWN	G.M.Chen		2015/5/22			
							CHECKED					TITLE: CONNECTOR	
							APPROVALS					PART NO. DW127S-22-XX-43	
	A		NEW				TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	SHEET 1 OF 1
						10~30		±0.20					
						5~10		±0.15					
						~ 5		±0.10					
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.			±2'	DRAWING NO.		PROJ: 	