





A B C D E F



N=PIN数



Material 材料  
 Insulator 塑胶: PBT PA9T (UL 94V-0)  
 Contact 端子: Brass 黄铜  
 Surface Coating 表面镀层: Gold Over Nickel 里镍外金  
 Electrical Characteristics 电气特性  
 Current rating 额定电流: 2.5Amps  
 Dielectric Withstanding Voltage 耐压:  
 AC 500V for 1 Minute.  
 Insulator Resistance 绝缘电阻: 1000MΩ Min.  
 Contact Resistance 接触电阻: 20mΩ Max.  
 Operating Temperature 工作温度: -40°C ~ +105°C  
 Max. Processing Temp 瞬时温度:  
 240° C for 30-60 seconds  
 (260° C for 10 seconds)

P.C.B LAYOUT

未注尺寸公差			2.54-1*N		上海洲日电子有限公司			
公差					Shanghai Zhouri Electronics CO.,LTD			
尺寸	长度	角度	版本编号 20171018 A/O		上海康司玛电子设备进出口有限公司			
X.	±0.3	±5°			Shanghai KangSiMa Eletronic Equipment			
X.X	±0.2	±3°			import and export Co.,LTD			
X.XX	±0.15				TEL:86-21-34975176/51571121			
制图	周元金	201171018	图纸编号	ZR20171018-256				
审核	张海娜	201171018	物料编号		1:1	mm	图幅	A4
核准	章妹	201171018	第三视角					1 1

A B C D E F