










专利产品 工程图



料号备注

ZH CT 2 F 021 M XX R XX XX

01=半金雾锡1U"	R=ROHS2.0标准
02=半金雾锡3U"	W=无卤+ROHS2.0
03=半金雾锡5U"	B=盐雾24H
04=半金雾锡10U"	H=REACH标准
05=半金雾锡15U"	C=盐雾48H

A12	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1
GND			VBUS				CC1				
B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12
GENERAL TOLERANCES: (UNLESS SPECIFIED)											
MILLIMETERS	INCH	PROJECTION		深圳市艾联特电子科技有限公司							
. = ±.30	. = ±.0150	D.R. 2021/07/06		TITLE TYPE C 6P 板上SMT防水母							
.X = ±.25	.X = ±.0098	MILES		座L=7.5mm, 带柱两DIP脚防水X8级 B款							
.XX = ±.20	.XX = ±.0059	CH.K 2021/07/06		DET. NO: WI-CPC-0021-00							
.XXX = ±.10	.XXX = ±.0020	MILES		MOULD NO: B0404-ATCF-06-005							
X° = ± 1°	X° = ± 2°	APV.D		SIZE: A4							
X.XX° = ± 0.5°	X.XX° = ± 1°	P/N: ZHCT2F021M01R00RC		SCALE: 1:1							
		REV: A		REV: A							
		SH,T NO: 1OF1		SH,T NO: 1OF1							

- 备注(NOTE):
- 材质:
 - 1-1. 塑胶: PA9T 黑色UL94V-0, 符合环保。
 - 1-2. 端子: C2680-H T, 镀半金雾锡1U"。
 - 1-3. 外壳: SUS201-1/2H 镀镍48H, 符合SGS环保。
 - 尺寸标注事项:
 - 2-1. 图示有标注“▲”记号者为重点尺寸。
 - 2-2. 图示所有标注“*”尺寸为首样全检尺寸。
 - 2-3. 图示所有标注“Cpk”尺寸为Cpk检验尺寸。
 - 电气特性:
 - 3-1. 接触区: 接触电阻40mΩ Max, 允许10mΩ变化量。测试条件: 20mV, 100mA下测量。
 - 3-2. 接触电流: 3A VBUS引脚; 1.25A用于GND引脚; 其他引脚为0.25A。
 - 3-3. 额定电压: 30V.
 - 3-4. 耐电电压: 100VR.M.S.
 - 3-5. 绝缘电阻: 至少100兆欧。
 - 机械性能:
 - 4-1. 插入力: 0.51-2.04Kg, 拔出力: 0.51-2.04Kg
 - 4-2. 插拔次数: 10000次。
 - 工作环境: -20°C to +85°C.
 - 测试要求:
 - 6-1. 吃锡测试: 95%, 盐雾测试: 24HR MIN.
 - 品质要求事项:
 - 7-1. 产品表面不能刮伤, 划伤压痕, 缺胶, 歪PIN, 起气泡。
 - 7-2. 镀层要均匀, 不能有发黑发白及露铜现象。